

Acculux SL5 LED Set

Work and Emergency Lamp Enclosure type IP 54











Hand lamp with 3 Watt Power LED and charging station

Description

Rechargeable hand lamp for professional use incl. diffuser orange e.g. as a blinking emergency lamp.

Emergency light function at charging station according VDE 0108. The Power LED delivers a **bright and homogeneous light** for the work area.

There is no change of a bulb needed any more.

Extremely light-weight of the lamp

Ergonomic and easy-to-use design

Dust- and splash-proof

110° swivelling lamp head

3 Watt Power LED as main lamp with automatic switch to pilot lamp Remaining capacity indicator by 4 LED; the charging level is indicated by flashing of the pilot lamp. The charger features an optimised charging function and still is very compact; this allows it to be installed in the smallest niche in a vehicle or building. The AccuLux SL 5 LED can be charged at 230 V AC as well as 24 or 12 V DC.

High-quality and maintenence-free lead gel battery.

Technical Data

Article-No.
Casing material
Enclosure type of lamp
Main lamp
Operating time, main lamp
Operating time, blinking
Life time of the LED
Luminous flux, main lamp
Beam range
Pilot lamp
Operating time, pilot lamp
Rechargeable battery

Charging time
Charging voltage
Protection class
Laser class
Weight of lamp
Dimensions in mm (Set)

AccuLux SL 5 LED Set

456441 plastics IP 54 3 Watt Power LED approx. 5 h approx. 10 h up to 50.000 h 170 Im approx. 150 m Nichia LED 5 mm approx. 75 h lead gel battery, 4V/3,5Ah maintenance-free approx. 15 h 230V AC 50/60Hz, 12/24V DC Ш 1 1100 g

Set including

Emergency lamp SL 5 LED with charger L 5. Orange frontglas, connecting cable 230V with euro-plug, connecting cable 12/24V with mounted plug for cigarette lighters in cars and users manual.

104x245x120

