

Product data sheet

Specifications



APC Smart-UPS X Battery pack for Extended runtime, Rack/Tower 2U, 120Vdc

SMX120RMBP2U

Product availability : Stock - Normally stocked in distribution facility

Overview

Lead time Usually Ships within 2 Weeks

Main

Product or Component Type	Battery
Number of rack unit	2U
Battery Type	Lead-Acid battery
Provided Equipment	Installation guide Rack Mounting brackets

Batteries & Runtime

Battery blocks per string	10
Device mounting	Enclosed battery cartridge
Included Battery Modules	0
Battery Slots Empty	0
RBC Quantity	2
Battery Voltage	120 V
Replacement battery	APCRBC118

Physical

Color	Black
Height	3.35 in (8.5 cm)
Width	17.01 in (43.2 cm)
Depth	26.26 in (66.7 cm)
Net Weight	124.25 lb(US) (56.36 kg)
Mounting Mode	Rack-mounted
USB compatible	No

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %

Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304295839
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.57 in (24.3 cm)
Package 1 Width	23.46 in (59.6 cm)
Package 1 Length	34.21 in (86.9 cm)
Package 1 Weight	140.30 lb(US) (63.64 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	6
Package 2 Height	34.25 in (87 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	859.80 lb(US) (390 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)