

Silicon Power Blaze B05 USB flash drive 8 GB USB Type-A 3.2 Gen 1 (3.1 Gen 1) Black

Brand : Silicon Power

Product code: SP008GBUF3B05V1K

Product name : Blaze B05

USB 3.0 /USB 2.0/ USB 1.1, 8GB

Silicon Power Blaze B05 USB flash drive 8 GB USB Type-A 3.2 Gen 1 (3.1 Gen 1) Black:



LED indicator

Blaze B05 are designed with a LED indicator by which users can easily recognize the transferring status with just a simple glance.

Simply a thumb needed, easily everything completed

The intelligent adoption of the "retractable USB connector" promises users an easier and more efficient way for daily use by which users just need to operate with one thumb only.

Brighten Up Speed Up

Blaze B05 come in the modern look with the stylish and stream shape design and various vivid color schemes including classic black, navy blue and sweet pink



USB 3.0 Ultra Fast Transfer Rate

outstanding read/write speed is coupled with the latest USB 3.0 interface feature a 5Gb/s bandwidth which is 10x the bandwidth of a USB 2.0 interface. It saves users precious time backing up to and from the hard drive when transferring mass data files.

Performance		Performance	
Capacity *	8 GB	Linux operating systems supported	✓
Device interface *	USB Type-A	Design	
USB version *	3.2 Gen 1 (3.1 Gen 1)	Form factor *	Cap
	Windows 7 Home Basic,Windows 7 Home Basic x64,Windows 7 Home Premium,Windows 7 Home Premium x64,Windows 7 Professional,Windows 7 Professional x64,Windows 7 Starter,Windows 7 Starter x64,Windows 7 Ultimate,Windows 7 Ultimate x64,Windows 8,Windows 8 Enterprise,Windows 8 Enterprise x64,Windows 8 Pro,Windows 8 Pro x64,Windows 8 x64,Windows Vista Business,Windows Vista Business x64,Windows Vista Enterprise,Windows Vista Enterprise x64,Windows Vista Home Basic,Windows Vista Home Basic x64,Windows Vista Home Premium,Windows Vista Home Premium x64,Windows Vista Ultimate,Windows Vista Ultimate x64,Windows XP Home,Windows XP Home x64,Windows XP Professional,Windows XP Professional x64	Product colour *	Black
Windows operating systems supported		Weight & dimensions	
		Width	20 mm
		Depth	10 mm
		Height	53.9 mm
		Weight	9.2 g
Mac operating systems supported	Mac OS X 10.3 Panther		



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.