

2.5" SATA III Solid State Drives Slim Series

Slim S80

Dimension	100.0 x 69.9 x 7.0mm
Weight (max.)	63g
Flash type	MLC
Vibration	20G
Shock	1500G Max
Power requirement	5V
Transfer speed	Up to R/W 550/540MB/s (ATTO)
Warranty	3 years



240GB	SP240GBSS3S80S25	960GB	SP960GBSS3S80S25
480GB	SP480GBSS3S80S25		

Slim S60

Dimension	100.0 x 69.9 x 7.0mm
Weight (max.)	63g
Flash type	MLC
Vibration	20G
Shock	1500G Max
Power requirement	5V
Transfer speed	Up to R/W 560/500MB/s (ATTO)
Warranty	3 years



32GB	SP032GBSS3S60S25	240GB	SP240GBSS3S60S25
60GB	SP060GBSS3S60S25	480GB	SP480GBSS3S60S25
120GB	SP120GBSS3S60S25		

Solid State Drive Upgrade Kit Slim S55/S60 plus Shockproof Enclosure

Content	S55/S60 solid state drive	Slim S55 Upgrade Kit	120GB SP120GBSS3S55S27	Slim S60 Upgrade Kit	120GB SP120GBSS3S60S27
	Shockproof HDD enclosure		240GB SP240GBSS3S55S27		240GB SP240GBSS3S60S27
	"NTI Echo 3" clone software		480GB SP480GBSS3S55S27		480GB SP480GBSS3S60S27
			960GB SP960GBSS3S55S27		

- System upgrade solution for small budgets
- Turns a left over hard drive into a shockproof portable hard drive
- Free cloning software "NTI Echo 3" included for data and system backups
- Only for 7mm HDD



**Note: Performance result may vary, depending on system platform, software, interface and capacity. Please go to our website for more detailed information.

2.5" SATA III Solid State Drives Slim Series / Ace Series

Slim S55

Dimension	100.0 x 69.9 x 7.0mm
Weight (max.)	63g
Flash type	TLC
Vibration	20G
Shock	1500G Max
Power requirement	5V
Transfer speed	Up to R/W 560/530MB/s (ATTO)
Warranty	3 years



60GB	SP060GBSS3S55S25	480GB	SP480GBSS3S55S25
120GB	SP120GBSS3S55S25	960GB	SP960GBSS3S55S25
240GB	SP240GBSS3S55S25		

Ace A55

Dimension	100.0 x 69.9 x 7.0mm
Weight (max.)	63g
Flash type	TLC
Vibration	20G
Shock	1500G Max
Power requirement	5V
Transfer speed	Up to R/W 560/530MB/s (ATTO)
Warranty	3 years



64GB	SP064GBSS3A55S25	512GB	SP512GBSS3A55S25
128GB	SP128GBSS3A55S25	1TB	SP001TBSS3A55S25
256GB	SP256GBSS3A55S25		

Slim S56

Dimension	100.0 x 69.9 x 7.0mm
Weight (max.)	63g
Controller	Phison
Flash type	TLC
Vibration	20G
Shock	1500G Max
Power requirement	5V
Transfer speed	Up to R/W 560/530MB/s (ATTO)
Warranty	3 years



120GB	SP120GBSS3S56B25	480GB	SP480GBSS3S56A25
240GB	SP240GBSS3S56B25	960GB	SP960GBSS3S56A25

Ace A56

Dimension	100.0 x 69.9 x 7.0mm
Weight (max.)	63g
Controller	Phison
Flash type	TLC
Vibration	20G
Shock	1500G Max
Power requirement	5V
Transfer speed	Up to R/W 560/530MB/s (ATTO)
Warranty	3 years



64GB	SP064GBSS3A56B25	512GB	SP512GBSS3A56A25
128GB	SP128GBSS3A56B25	1TB	SP001TBSS3A56A25
256GB	SP256GBSS3A56B25		

Slim S57

Dimension	100.0 x 69.9 x 7.0mm
Weight (max.)	63g
Flash type	TLC
Vibration	20G
Shock	1500G Max
Power requirement	5V
Transfer speed	Up to R/W 535/410MB/s (ATTO)
Warranty	3 years



120GB	SP120GBSS3S57A25
240GB	SP240GBSS3S57A25

**Note: Performance result may vary, depending on system platform, software, interface and capacity. Please go to our website for more detailed information.