


SP



NEED FOR SPEED CHARGING



**MORE SPEED
LESS TIME**

The QM25 delivers a fast charge via the USB Type-A and Type-C ports to refuel mobile phones, tablets, some laptops, and more. Leverage Power Delivery (PD) via the Type-C output or QC3.0 via the USB Type-A output to take charge of your life and spend less time tethered to a wall – refuel your mobile phones from 0% to up to 50% in just 30 minutes!

Get up to 30W of charging power for less – the QM25 is 20% smaller and 35% lighter than the standard 30W Apple charger! Its compact form factor also ensures an outlet fit that won't interfere with space for other chargers and makes it the ideal choice for tossing in your bag and taking with you for all device replenishment needs.



**MORE POWER
LESS SPACE**

Wall Charger QM25

Features

- Delivers up to 30W of charging power via the USB Type-A and Type-C ports to refuel mobile phones, tablets, some laptops, and more
- Ready to fast charge compatible devices with Power Delivery (PD) via Type-C and QC3.0 via USB Type-A*†
- 20% smaller and 35% lighter than the standard 30W Apple charger
- Fast and efficient charging for all Apple devices including the new iPhone 14 Series, MacBook Air, and iPad
- Supports the Samsung Super Fast Charging (SFC) protocol on compatible devices such as the new Galaxy S22 Series
- High-quality construction extends the charger's life and improves overall performance
- Compact form factor ensures maximum portability as well as an outlet fit that won't interfere with space for other chargers
- Safety measures including over voltage protection, over current protection, short circuit protection, and UL94V0 (flame-retardant) provide total protection for you and your devices

* Only one device may be connected to the charger at a time in order for fast charging to be enabled
† PD is supported by Android-based and iOS-based devices, while QC3.0 is only supported by Android-based devices (excluding some Huawei and OPPO models)

Specifications

- Total Power Output: 30W
- Input: AC100-240V, 50/60Hz Max 0.75A
- Output: USB (USB Type-A): 5V=3A, 9V=2A, 12V=1.5A ; Type-C: 5V=3A, 9V=3A, 12V=2.5A, 15V=2A, 20V=1.5A ; USB + Type-C: 5V=3.0A (max.)
- Dimensions: US: 48.0mm x 44.8mm x 31.5mm
- Weight: 65g
- Material: PC (UL94V0 Grade)
- Color: White
- Available Interface (Output): USB Type-A (x1), Type-C (x1)
- Available Interface (Input): US or EU Plug
- Operating Temperature: 0°C - 40°C
- Protection: Over-Voltage Protection, Over-Current Protection, Short-Circuit Protection, Surge Protection, Flame-Retardant (UL94V0 Grade)
- Certification: ETL, BSMI, CE, FCC, PSE, RoHS, WEEE, ERP VI
- Warranty: 1 year