



Charge it in Style

GD27/GP27

A Look That Won't Weigh You Down

Thoughtfully designed, the GD27 and GP27 have a sleek metal surface with a semi-matte finish. Not only do they look great, but their slim and lightweight bodies also provide maximum portability and carrying ease. What's better than a power bank that disappears into your pocket or bag, unnoticed, but is stylishly eye-catching when you're ready to take it out and power up your devices?



An On-The-Go Power Boost

With 5,000mAh and 10,000mAh capacity, respectively, the GD27 and GP27 have just enough juice to fuel you throughout the day while you're out running errands, taking a day-trip, or cozying up in a café. Plus, 2 USB Type-A outputs allow up to 2 devices to charge simultaneously, because multi-tasking is a necessity for every aspect of life, nowadays.



Power Bank

GD27/GP27



smartSENSE



smartFOCUS



smartSHIELD

Features

- 5,000mAh/10,000mAh capacity provides 1-2/2-4 full charge cycles on just about any smartphone
- 2 USB Type-A outputs charge up to 2 devices simultaneously
- Sleek metal surface with a semi-matte finish adds a touch of style to your charging routine
- LED light charging status indicator
- smartSHIELD: Input High-Voltage Protection, Output High-Voltage Protection, Input Current Protection, Output Current Protection, Automatic Current Matching, Input Short-Circuit Protection, Output Short-Circuit Protection, Device Overcharge Protection, Reverse Charge Protection, Input Current Regulation, Static Resistance, and Fireproof Guard
- High quality Li-Polymer battery is safer, thinner, and provides a more effective charge
- Includes 1 USB Type-A to Micro-USB cable
- Safe to fly with
- Up to 2 million USD product liability insurance

Specifications

- Capacity: GD27: 5,000mAh(18.5wh/3.7v) / GP27: 10,000mAh(37wh/3.7v)
- Dimensions: GD27: 103.0mm x 64.0mm x 12.6mm
GP27: 138.0mm x 69.0mm x 14.5mm
- Weight: GD27: 116g / GP27: 207g
- Battery Type: Li-Polymer
- Material: Metal and PC+ABS
- Color: Black, Silver, Royal Blue(GD27), Green(GP27)
- Input Power: 5V/2A
- Output Power: USB1 (USB Type-A): 5V/2.1A, USB2 (USB Type-A): 5V/2.1A ;
USB1+USB2: 5V/2.1A (max.)
- Available Interface (Input): Micro-USB
- Available Interface (Output): USB Type-A (x2)
- Charging Time: GD27: 3 hours / GP27: 6 hours (2.0A power adapter suggested)
- Operating Temperature: 0°C - 40°C
- Certification: CE, FCC, BSMI, PSE, RoHS 2.0
- Warranty: 13 months, 2 years (EU)