

ENSTO

SPCM182508G

Cubo S enclosure

Code	SPCM182508G
GTIN	6418677166495
Name	Cubo S enclosure Ensto Cubo S Size 175 x 250 x 75 mm, 50 mm base, metric knockouts, grey cover, PC
Description	Ensto Cubo S is a series of small to medium size enclosures available with knockouts or plain sides. The base of the enclosures is equipped with unique slots for printed circuit boards.



Technical specification

Technical specification

Content:	Enclosure base, cover, cover screws, mounting screws
-----------------	---

Dimensions

Weight:	0.63 kg
Width:	175 mm
Volume :	328.13 cm ³
Size:	175 x 250 x 75
Height:	250 mm
Depth:	75 mm
Inner depth:	60.5 mm
Outer base depth:	50 mm
Outer cover height:	25 mm

Temperatures

Operating temperature:	-40 ... +80 °C
Short term temperature range:	-40 ... +120 °C

Materials

Base:	Fiberglass reinforced polycarbonate
Cover:	Polycarbonate

Cover screws:	Polyamide
Gasket:	Polyurethane
Material selection:	Polycarbonate

Colors

Color:	Grey
---------------	------

Features

Knockouts:	4 x M12/20 + 4 x M16/25 + 12 x M12/20
-------------------	---------------------------------------

Mechanical

Impact strength:	IK 08
-------------------------	-------

Certificates

Standards:	EN 62208, GOST R
-------------------	------------------

Ratings

Degree of protection:	IP66/IP67
Flammability rating:	UL 746C 5 inch flame test
ETIM class:	EC000261

ETIM

ETIM

Width:	175 mm
Colour:	Grey
Material:	Plastic
Height:	250 mm
Depth:	75 mm
Type of surface:	Untreated
RAL-number:	7035
Wall fastening possible:	true
Suitable for outdoor set-up:	true
Impact strength:	IK08
Degree of protection (IP):	IP67
Pole fastening:	false
With glazed door:	false
Tackable:	false
Wall build in:	false
Pitched roof:	false
EMC-version:	false
With ventilation door:	false
With backside door:	false
Floor installation possible:	false

Packaging

Default package

Unit:	PCS
Size:	1