

KERN SP 200K

KERN

Compact photometer, optimised for accurate light measurement, including LED light measurement



Category

Brand	Sauter
Product category	Environment/ Occupational safety
Product group	Light measuring instrument

Measuring System

Readability illumination [d] (lx)	0,1 lx; 1 lx; 10 lx; 100 lx
Measuring range [Max] (Lux)	200 lx; 2000 lx; 20000 lx; 200000 lx
Tolerance (% of [Max])	5%
Units	lx fc
Measuring head measuring frequency	2 Hz

Approval

CE mark	✓
---------	---

Display

Display digit height	16 mm
----------------------	-------

Construction

Dimension housing (W×D×H)	185×68×38 mm
Dimensions completely mounted (W×D×H)	185×68×38 mm
Material housing	plastic
Material display housing	Plastics

Functions

Hold function	✓
Peak function	✓

Power Supply

Supplied plug-in power supply	Battery
Battery	9 V block
Battery operating time	200 h

Packing & Shipping

Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	200×106×55 mm
Net weight approx.	0,15 kg
Gross weight approx.	0,30 kg
Shipping weight	0,28 kg

Services (optional)

Article number for factory calibration	961-190
---	---------

Piktogramme

STANDARD



OPTION

