



## SRPE 15-0

SPIRAL HOSE, BLACK, UL94-HB 15.0 mm, 10.0 m

For cables, tubes and conduits. Halogen free, non-flammable, heat-resistant and UV-resistant (black). Has high flexibility and provides very good protection against mechanical impact. Spirals are cut counter-clockwise. Supplied in bag or on reel.

## Product Properties:

<b>Model</b>	Spiral hose
<b>Material quality</b>	Polyethylene (PE)
<b>Transparent</b>	No
<b>Colour</b>	Black
<b>Fire classification</b>	According to UL94HB
<b>Material</b>	Plastic
<b>UV resistant</b>	Yes
<b>Halogen free</b>	Yes
<b>Operating temperature</b>	-40-100 °C

## Dimensions:

<b>Unit</b>	pck
<b>Wall thickness</b>	1 mm
<b>Nominal diameter</b>	15 mm
<b>Bundle diameter</b>	12-70 mm
<b>MOQ</b>	1 .

## Approvals:

## Compliance:

RoHS

RoHS 3 (2015/863)

<b>Conflict minerals</b>	N/A, Contains no conflict minerals
<b>Reach</b>	No SVHC (209 Subs. June 2020)
<b>US TSCA</b>	No (5 PBT Subs, Feb 2021)

### **Other information:**

<b>Trademark</b>	Thomas & Betts
<b>ETIM-Class</b>	EC002604 - Cable bundle hose
<b>ETIM-Release</b>	7.0
<b>Product Group</b>	Spiral wrap
<b>Search Description</b>	SRPE-15-0, 7TCG054090R0222
<b>Alternative SKU</b>	SRPE15-0

### **Logistic information:**

<b>Barcode</b>	541436317469
<b>Country of origin</b>	TH
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales.
<b>Stock code</b>	SRPE 15-0
<b>Taric code</b>	39269097
<b>Unit</b>	pck
<b>MOQ</b>	1 .