



SRPE 8-0

SPIRAL HOSE, BLACK, UL94-HB 8.0 mm, 10.0 m

For cables, tubes and conduits. Halogen free, non-flammable, heat-resistant and UV-resistant (black). Has high flexibility and provides very good protection against mechanical impact. Spirals are cut counter-clockwise. Supplied in bag or on reel.

Product Properties:

Model	Spiral hose
Material quality	Polyethylene (PE)
Transparent	No
Colour	Black
Fire classification	According to UL94HB
Material	Plastic
UV resistant	Yes
Halogen free	Yes
Operating temperature	-40-100 °C

Dimensions:

Unit	pck
Wall thickness	0,5 mm
Nominal diameter	8 mm
Bundle diameter	6-60 mm
MOQ	1 .

Approvals:

Compliance:

RoHS

RoHS 3 (2015/863)

Conflict minerals	N/A, Contains no conflict minerals
Reach	No SVHC (209 Subs. June 2020)
US TSCA	No (5 PBT Subs, Feb 2021)

Other information:

Trademark	Thomas & Betts
ETIM-Class	EC002604 - Cable bundle hose
ETIM-Release	7.0
Product Group	Spiral wrap
Search Description	SRPE 8-0, 7TCG054090R0238
Alternative SKU	SRPE8-0

Logistic information:

Barcode	541436317467
Country of origin	TH
Item status	Stock item, normally in stock with reservation for in between sales.
Stock code	SRPE 8-0
Taric code	39269097
Unit	pck
MOQ	1 .