

# APC Smart-UPS SRT 192V 8 and 10kVA RM Battery Pack

## SRT192RMBP2

Call for More Information



- Includes: Installation guide, Rack mounting brackets, Warranty card

Output	
Battery Output Voltage	+/- 192 V
Batteries & Runtime	
Battery type	Lead-acid battery
Battery mounting	Stand alone battery stack
Expected Battery Life (years)	3 - 5
RBC Quantity	2
Physical	
Maximum Height	130MM, 13.0CM
Maximum Width	432MM, 43.2CM
Maximum Depth	683MM, 68.27CM
Rack Height	3U
Net Weight	91.0KG
Shipping weight	105.5KG
Shipping Height	420MM, 42.0CM
Shipping Width	600MM, 60.0CM
Shipping Depth	1000MM, 100.0CM
Color	Black
Environmental	
Operating Temperature	0 - 40 °C

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

## Technical Specifications

Environmental	
Operating Relative Humidity	0 - 95 (Non-condensing) %
Operating Elevation	0 - 3048meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 (Non-condensing) %
Storage Elevation	0 - 15240meters

Conformance	
Approvals	OSHPD
Standard warranty	2 years repair or replace

Sustainable Offer Status	
RoHS	Compliant
Proposition 65 Warning	Available in Documentation tab

**Disclaimer:** Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.