

## Technical Specifications

APC Smart-UPS On-Line, 2200VA, Rackmount 2U, 230V, 6x C13+2x C19 IEC, SmartSlot, Extended runtime, W/ rail kit, W/O Lithium-ion external battery | SRT2200UXI-LI | Downloaded on 10/19/2023 (EST)

# APC Smart-UPS On-Line, 2200VA, Rackmount 2U, 230V, 6x C13+2x C19 IEC, SmartSlot, Extended runtime, W/ rail kit, W/O Lithium-ion external battery

SRT2200UXI-LI

Call for More Information 800 10 436



- High density, double-conversion on-line power protection with scalable runtime.
- Includes: CD with software, Communication cable, Documentation CD, Installation guide, Removable support feet, USB cable, Warranty card

Output	
Output power capacity	1.98kWatts / 2.2kVA
Max Configurable Power (Watts)	1.98kWatts / 2.2kVA
Nominal Output Voltage	230V
Output Voltage Distortion	Less than 2 %
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz Sync to mains
Other Output Voltages	220 V, 240 V
Load Crest Factor	3 : 1
Topology	Double conversion online
Waveform type	Sine wave
Output Connections	(6) IEC 60320 C13 (2) IEC 60320 C19
Bypass	Built-in bypass

Input	
Nominal Input Voltage	230V
Input frequency	40 - 70 Hz Auto-sensing
Input Connections	BS1363A British, IEC 60320 C20, Schuko CEE 7 / EU1-16P
Cord Length	1.8meters
Input voltage range for main operations	50 - 150 40% load, 80 - 150V
Number of Power Cords	1
Other Input Voltages	220 V, 240 V

**Disclaimer:** Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

## Technical Specifications

APC Smart-UPS On-Line, 2200VA, Rackmount 2U, 230V, 6x C13+2x C19 IEC, SmartSlot, Extended runtime, W/ rail kit, W/O Lithium-ion external battery | SRT2200UXI-LI | Downloaded on 10/19/2023 (EST)



Batteries & Runtime	
Battery type	Lead-acid battery
Extendable Run Time	1
Efficiency	View Efficiency Graph (Available in Technical Tab on site)

Communications & Management	
Interface Port(s)	RJ-45 Serial, Smart-Slot, USB
Emergency Power Off (EPO)	Yes
Available SmartSlot™ Interface Quantity	1

Surge Protection and Filtering	
Surge energy rating	432Joules

Physical	
Maximum Height	432MM, 43.2CM
Maximum Width	85MM, 8.5CM
Maximum Depth	508MM, 50.8CM
Rack Height	2U
Net Weight	22.0KG
Shipping weight	29.6KG
Shipping Height	246MM, 24.6CM
Shipping Width	749MM, 74.9CM
Shipping Depth	594MM, 59.4CM
Color	Black

Environmental	
Operating Temperature	0 - 40 °C
Operating Relative Humidity	0 - 95 (Non-condensing) %
Operating Elevation	0 - 3048meters
Storage Temperature	-20 - 50 °C
Storage Relative Humidity	0 - 95 (Non-condensing) %
Storage Elevation	0 - 15240meters

**Disclaimer:** Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

## Technical Specifications

APC Smart-UPS On-Line, 2200VA, Rackmount 2U, 230V, 6x C13+2x C19 IEC, SmartSlot, Extended runtime, W/ rail kit, W/O Lithium-ion external battery | SRT2200UXI-LI | Downloaded on 10/19/2023 (EST)

Environmental	
Audible noise at 1 meter from surface of unit	50.0dBA
Online thermal dissipation	317.0BTU/hr
Protection Class	IP20

  

Conformance	
Approvals	CE, EAC
Standard warranty	5 year repair or replace

  

Sustainable Offer Status	
RoHS	Compliant

**Disclaimer:** Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.