

Product data sheet

Specifications



APC Smart-UPS On-Line, 3kVA, Lithium-ion, Rackmount 4U, 230V, 6x C13+2x C19 IEC outlets, Network Card, Extended long runtime, Rail kit included

SRTL3000RM4UXLI-NC

Overview

Presentation	High density, double-conversion on-line power protection with long runtime with NMC
Lead time	Usually in Stock

Main

Main Input Voltage	230 V
Other Input Voltage	220 V
Main Output Voltage	230 V
Other Output Voltage	220 V
Rated power in W	2700 W
Rated power in VA	3000 VA
Input Connection Type	IEC 60320 C20
Output connection type	6 IEC 60320 C13
Number of rack unit	4U
Cable length	1.83 m
Number of cables	1
Battery type	Li-Ion (Lithium-Ion)

General

Product web sub-family	Lithium-Ion
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Colour	Black with silver front bezel
Height	17.1 cm
Width	43.2 cm
Depth	63.9 cm

Net weight	44.5 kg
Mounting preference	No preference
Mounting mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes
Mounting position	Horizontal Vertical

Input

Network frequency	40...70 Hz auto-sensing
Input voltage limits	160...275 V

Output

Maximum configurable power in W	2700 W
Harmonic distortion	Less than 2 %
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Crest factor	3 : 1
UPS type	Double conversion online
Wave type	Sine wave
Bypass type	Built-in bypass
Maximum configurable power in VA	3000 VA

Conformance

Product certifications	CE
Marking	CE Mark

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-20...50 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0.00...15240.00 m
Acoustic level	50 dBA
Heat dissipation	317 Btu/h
IP degree of protection	IP20

Batteries & Runtime

Number of battery filled slots	0
Number of battery free slots	0
Battery voltage	48 V
Battery charger power	158 W rated
Battery power in VAH	2400 VAh capacity

2880 VAh runtime

Battery life	5...10 year(s)
Battery option	XBP48RM2U-LI 1 5760 VAh XBP48RM2U-LI 2 8640 VAh
Extended runtime	1

Communications & Management

Free slots	0
Preinstalled device	Network management card 2 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity
Emergency power off	Yes

Surge Protection and Filtering

Surge energy rate	432 J
--------------------------	-------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes

Contractual warranty

Warranty	5 year repair or replace
-----------------	--------------------------

Recommended replacement(s)