

2 Port HDMI KVM Switch - 4K 60Hz - Compact Dual Port UHD/Ultra HD USB Desktop KVM Switch w/Integrated 4ft Cables & Audio - Bus Powered & Remote Switching - MacBook ThinkPad

Product ID: SV211HDUA4K



The SV211HDUA4K 2-Port 4K60Hz HDMI Cable KVM Switch with Audio and Remote Switching Control gives you control of two HDMI, USB equipped computers with a single monitor, keyboard, mouse and audio peripheral set.

The Dual HDMI KVM switch supports resolutions up to 4K at 60Hz and can drive one large HDMI display with ease, maximizing viewing space. With support for separate 3.5 mm stereo audio, the KVM switch delivers full audio compatibility across connected computers.

While supporting most PC operating systems, this HDMI KVM switch is OS independent which means it works with Mac computers (an adapter may be required) and any other laptops, notebooks, and tablets.

The switch features a remote push-button on a 1.5 meter (4ft) integrated cable that can be placed in an easily accessible location, as well as keyboard hot-keys, and PC or Mac compatible software for switching between systems.

StarTech.com offers a wide selection of high-quality KVM switches and KVM-related products to help you access your systems more efficiently without the expense and clutter of extra keyboards, mice and monitors.

The SV211HDUA4K is backed by a 2-year StarTech.com warranty and free lifetime multilingual technical support.

Certifications, Reports and Compatibility

Applications

Features

- Operate and access two HDMI computers from one workstation at 4K 60Hz resolutions

- Integrate into your set up quickly and easily with built-in 4 ft. KVM cables (including remote switch) and a space-saving design
- Switch PCs via push-button, hot-keys or switching software
- Switching software supports Windows, Windows Server & macOS platforms
- USB Powered - No external power adapter required
- Independent audio/mic switching for uninterrupted audio Analog (3.5mm) and HDMI audio supported

Hardware

| | |
|------------------------------|---------|
| Warranty | 2 Years |
| Audio | Yes |
| KVM Ports | 2 |
| PC Interface | USB |
| PC Video Type | HDMI |
| Number of Monitors Supported | 1 |
| Rack-Mountable | No |
| Cables Included | Yes |
| Daisy-Chain | No |

Performance

| | |
|-----------------------------|------------------------------------|
| On-Screen Display | No |
| IP Control | No |
| Hot-Key Selection | Yes |
| Maximum Data Transfer Rate | 480Mbps (USB 2.0) |
| Maximum Digital Resolutions | 3840 x 2160 (Ultra HD 4K) @ 60hz |
| Wide Screen Supported | Yes |
| Audio Specifications | Two Channel Audio Input and Output |
| Auto Scan | 10, 20, 30, 40, 50, and 60 seconds |



Port Selection Support Push Button, Hotkeys, and Software

MTBF 1,012,884 hours

Connector(s)

Console Interface(s) USB Type-A (4 pin) USB 2.0

HDMI

3.5 mm Mini-Jack (3 Position)

Host Connectors USB Type-A (4 pin) USB 2.0

HDMI

3.5 mm Mini-Jack (3 Position)

Software

OS Compatibility Windows 2000, XP, Vista, 7, 8, 8.1, 10

Windows Server 2003, 2008 R2, 2012, 2016, 2019

Mac OS 10.6 to 10.9

Special Notes / Requirements

Note In order to access the software and hotkeys of the KVMs, a compatible OS must be installed on the connected host, however the KVM and push button switching function is OS independent

Indicators

LED Indicators Orange

Power

Power Source Bus Powered

Environmental

Operating Temperature 0 ~ 40C

Storage Temperature -20 ~ 60C

Humidity 0 ~ 90% RH, Non-Condensing

Physical Characteristics

Product Length 4.3 ft [1.3 m]



| | |
|-------------------|-----------------|
| Product Width | 3.8 in [97 mm] |
| Product Height | 1.0 in [25 mm] |
| Weight of Product | 15.2 oz [431 g] |

Packaging Information

| | |
|---------------------------|-----------------|
| Package Length | 6.3 in [16 cm] |
| Package Width | 9.8 in [25 cm] |
| Package Height | 2.5 in [63 mm] |
| Shipping (Package) Weight | 18.4 oz [522 g] |

What's in the Box

| | |
|---------------------|-------------------|
| Included in Package | KVM Switch |
| | Quick-Start Guide |

****Product appearance and specifications are subject to change without notice.***

