

Long Range USB VGA KVM Console Extender over Cat5 UTP - 1000 ft

Product ID: SV565UTPUL



The SV565UTPUL Long Range USB VGA KVM Console Extender over Cat5 UTP (1000 ft) lets you control a server, computer or multiple computers (connected through KVM Switch) over a standard Cat5 or Cat6 UTP network cable connection, at distances of up to 1000ft (300m) away.

You can use your existing USB keyboard, USB mouse, and monitor to access both the server room and your office computer, saving space and avoiding the need for a dedicated remote console by allowing you to switch between workstation view and KVM view at the remote location.

This product is TAA compliant and backed by a Startech.com 3-year warranty with free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Allow two users to share one PC or KVM
- Control remote machines and security monitoring systems
- Use one or more servers in a server room from a remote location

- Monitor computer-controlled equipment in a factory or warehouse at a distance

Features


- High resolution support: Up to 1920x1200(WUXGA)/ 1600x1200(UXGA)
- Kit includes both local and remote units
- Compatibility mode enables hotkey commands to be passed to connected StarView KVMs
- Max Resolution Limit feature caps the resolution to prevent the resolution setting from exceeding the capability of the connected display
- USB computers are supported at the host and remote locations (USB keyboard and mouse required for remote console)
- Supports auto-switching between host and remote users or dedicated control
- Compatible with CAT 5, 5e, or 6 UTP cabling
- Intuitive hotkey commands
- Hotkey controlled Equalizer(sharpness), Gain(brightness), and RGB Skew adjustments
- Supports most combo keyboard and mouse sets (including Wireless)
- PS/2 and USB host PC's supported via the appropriate PS2 or USB KVM cable (USB style included)

Hardware

Warranty	3 Years
Audio	No
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes

Performance

IP Control	No
------------	----



Max Transfer Distance	300 m (984 ft)
Maximum Analog Resolutions	UXGA - 1600x1200, WUXGA - 1920x1200
Wide Screen Supported	Yes
Port Selection Support	Push Button and Hotkeys
MTBF	164000 hours

Connector(s)

Console Interface(s)	4 - USB 2.0 Type-A (4 pin, 480Mbps) 2 - VGA (15 pin, High Density D-Sub)
Host Connectors	2 - VGA (15 pin, High Density D-Sub)
Other Interface(s)	2 - RJ-45

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Special Notes / Requirements

Note	Supports most combo keyboard and mouse sets (including Wireless)
------	--

Indicators

LED Indicators	2 - Remote indicator 2 - Local indicator
----------------	---

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.8A
Output Voltage	12V DC
Output Current	1.5A
Center Tip Polarity	Positive
Plug Type	M



Power Consumption (In Watts) 18

Environmental

Operating Temperature 0C to 40C (32F to 104F)
Storage Temperature -20C to 60C (-4F to 140F)
Humidity 0~80% RH

Physical Characteristics

Color Black
Material Steel
Product Width 6.2 in [15.7 cm]
Product Height 0.8 in [2 cm]
Product Depth 2.8 in [70 mm]
Weight of Product 22.0 oz [622 g]

Packaging Information

Package Quantity 1
Package Length 11.6 in [29.4 cm]
Package Width 7.8 in [19.7 cm]
Package Height 2.8 in [72 mm]
Shipping (Package) Weight 3.0 lb [1.4 kg]

What's in the Box

Included in Package

- 2 - KVM Extenders (1x Local, 1x Remote)
- 2 - 2n1 USB VGA KVM Cables
- 1 - Rubber Feet
- 1 - Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand



1 - User Manual

****Product appearance and specifications are subject to change without notice.***

