



Class 10, UHS Speed Class 3  
Video Speed Class 30 (V30)<sup>2</sup>  
32GB, 64GB and 128GB\*

## SanDisk Extreme PRO<sup>®</sup> microSDHC & microSDXC UHS-I Card

Perform Like a PRO

### Highlights

- Fast microSD<sup>™</sup> UHS-I speeds for the ultimate smartphone, tablet and camera performance
- Up to 95MB/s\*\* read speed; up to 90MB/s\*\* write speed
- Ideal for your 4K Ultra HD and Full HD video-enabled smartphone, tablet or camera<sup>1</sup>
- The capacity you need to shoot and save the highest resolution videos and stills
- Pro Video Performance with Class 10 and UHS Speed Class 3 (U3) and Video Speed Class 30 (V30) ratings for capturing Full HD and 4K UHD video<sup>2</sup>
- RescuePRO<sup>®</sup> Deluxe data recovery software downloadable offer<sup>5</sup>, for bringing accidentally deleted images back to life

### Top speed meets high capacity

The SanDisk Extreme PRO<sup>®</sup> microSDHC<sup>™</sup>\_microSDXC<sup>™</sup> UHS-I cards now come in capacities of up to 128GB of storage for uncompromising smartphone, tablet and action camera performance. Capture Full HD and 4K UHD videos<sup>1</sup> and enjoy transfer speeds of up to 95MB/s\* so you can shoot like a pro and still experience world-class responsiveness from your phone. Class 10, UHS-I Speed Class 3 (U3)<sup>2</sup> and Video Speed Class 30 (V30) ratings mean your videos can meet today's highest resolution standards and will look stunning on the latest 4K UHD TV screens and monitors. Generous storage capacity means you won't run out of the memory you need to work, shoot and share.

### Extreme durability protects your best shots

SanDisk Extreme PRO cards are built tough for extreme durability even under challenging environmental conditions<sup>3</sup>—they're temperature proof, waterproof, shock proof, and X-ray proof. Whether you're shooting with your smartphone or your action camera, you can trust that you've captured those heart-in-the-mouth moments for posterity.

Mac to edit and store.

## SanDisk Extreme PRO<sup>®</sup> microSDHC & microSDXC UHS-I Card Specifications

<b>Form Factor</b>	microSDHC™, microSDXC™
<b>Available Capacities</b>	microSDHC: 32GB microSDXC: 64GB and 128GB*
<b>Performance/Speed</b>	Up to 95MB/s** read speed; write speed up to 90MB/s**
<b>Dimensions</b>	microSDHC: 0.43in x 0.59in x 0.04in (10.92mm x 14.99mm x 1.02mm)
<b>Operating Temperature</b>	-13°F to 185°F (-25°C to 85°C) <sup>vi</sup>
<b>Storage Temperature</b>	-40°F to 185°F (-40°C to 85°C) <sup>vi</sup>
<b>Compatibility</b>	Compatible with microSDHC™ and microSDXC™ supporting host devices
<b>Warranty</b>	Lifetime limited warranty <sup>6</sup> -US ONLY Lifetime warranty <sup>6</sup>



Terms and Conditions apply.

For more information, please visit  
www.sandisk.com

# SanDisk<sup>®</sup>

a Western Digital brand

At SanDisk, we're expanding the possibilities of data storage. For more than 25 years, SanDisk's ideas have helped transform the industry, delivering next generation storage solutions for consumers and businesses around the globe.

**Western Digital Technologies, Inc.**  
951 SanDisk Drive | Milpitas | CA 95035 | USA

**SanDisk International**  
Unit 100, Airside Business Park |  
Lakeshore Drive, Swords | Co Dublin | Ireland

Western Digital Technologies, Inc. is the seller of record and licensee in the Americas of SanDisk<sup>®</sup> products.

Not all devices support microSDXC™ memory cards.

\* Up to 95 MB/s read speed. Write speed up to 90 MB/s Based on internal testing; performance may be lower depending on host device. 1MB = 1,000,000 bytes.

\*\* 1GB = 1,000,000,000 bytes. Actual user storage less.

<sup>1</sup> Compatible device required. Full HD (1920x1080) and 4K UHD (3840 x 2160) video support may vary based upon host device, file attributes, and other factors. See: www.sandisk.com/HD.

<sup>2</sup> UHS Speed Class 3 designates a performance option designed to support 4K UHD video recording with UHS-I enabled host devices. 32GB-128GB ONLY: Video Speed Class 30 (V30), sustained video capture rate of 30MB/s, designates a performance option designed to support real-time video recording with UHS enabled host devices. See www.sdcard.org/consumers/speed.

<sup>3</sup> See product packaging and www.sandisk.com/proof for additional information and limitations.

<sup>4</sup> Compatible device required. UHS Speed Class 3 designates a performance option designed to support 4K UHD video recording with UHS-I enabled host devices. Full HD (1920x1080), and 4K UHD (3840 x 2160) video support may vary based upon host device, file attributes, and other factors. See: www.sandisk.com/HD.

<sup>5</sup> Registration required; terms and conditions apply.

<sup>6</sup> 30-year warranty in Germany, Canada, and regions not recognizing lifetime warranty. See www.sandisk.com/wug

SanDisk, RescuePRO, and SanDisk Extreme are trademarks of Western Digital Corporation or its affiliates registered in the United States and other countries. The SD, microSDHC, microSDXC, SDHC and SDXC marks and logos are trademarks of SD-3C, LLC. Android and Google Play are trademarks of Google Inc. The Android robot is reproduced or modified from work created and shared by Google and used according to terms described in the Creative Commons 3.0 Attribution License. Windows and the Windows logo are trademarks of the Microsoft group of companies. Mac is a trademark of Apple Inc. All other trademarks are the property of their respective owners.

© 2016 Western Digital Corporation or its affiliates. All rights reserved. 10/16