


SIMATIC S7-400, rack UR1, central and distributed with 18 slots, 2 redundant PS can be plugged in



| General information                               |  |
|---|--|
| Product type designation                          | UR1  |
| Hardware configuration                            |  |
| Rack  |  |
| • Communication bus                               | Yes  |
| • P bus   | Yes  |
| Slots   |  |
| • Number of slots                                 | 18   |
| Standards, approvals, certificates                |  |
| CE mark   | Yes  |
| UKCA mark   | Yes  |
| UL approval                                       | Yes  |
| FM approval                                       | Yes  |
| RCM (formerly C-TICK)                             | Yes  |
| KC approval                                       | Yes  |
| EAC (formerly Gost-R)                             | Yes  |
| CCC   | Yes  |
| Ambient conditions                                |  |
| Ambient temperature during operation              |  |
| • min.  | 0 °C   |
| • max.  | 60 °C  |
| Ambient temperature during storage/transportation |  |
| • min.  | 0 °C   |
| • max.  | 70 °C  |
| Dimensions  |  |
| Width   | 482.5 mm   |
| Height  | 290 mm   |
| Depth   | 27.5 mm  |
| Weights   |  |
| Weight, approx.                                   | 4.1 kg   |
| last modified:                                    | 8/7/2023  |