



SIEVI SAFETY FOOTWEAR 2018

Technical Information Data



Product **Active 2** Prod. No. **38-12225-513-95M** sizes 39—47

Standard

- EN ISO 20347: OB A E FO

Sizes

- 39—47

Last

- 11 (normal)

Upper

- microfiber, thickness 1.4 mm
- padded tongue and top line

Sole

- polyurethane material, direct injection moulded, featuring the following benefits:
 - excellent shock-absorption under the whole foot
 - light and flexible, slip resistant material

Insole

- synthetic, hygienic fibre, highly abrasion resistant
- antistatic and ESD

Lining

- synthetic Sievi 3D-dry material featuring the following benefits:
 - highly abrasion resistant, breathable
 - effectively absorbs perspiration moisture from the foot; dries fast
- heel grip of microfiber

Counter (stiffener)

- inserted between the lining and the upper to ensure a strong heel construction; the shoe holds its form well

Removable insole

- Sievi Comfort insock
- antistatic and ESD
- machine washable in 40 Celsius

Fastening

- two adjustable hook and loop fasteners in front
- one hook and loop fastener behind the heel

Other details

- fulfils the requirements of IEC 61340-5-1 for ESD footwear
- ESD-mark is labelled on the shoe
- completely metal free shoe
- Information leaflet is included in every shoe box

Sievi has

- Certified Quality Management System: ISO 9001
- Certified Environmental Management System: ISO 14001
- Certified Occupational Health and Safety System: OHSAS 18001