

# Type-A USB 3.2 Gen 1 interface allows for speedy data transfers up to 5 Gbps

---

 [silicon-power.com/web/gb/product-B07](https://silicon-power.com/web/gb/product-B07)



## More Power With USB 3.2 Gen 1

---

The Blaze B07 Type-A USB flash drive is equipped with a USB 3.2 Gen 1 interface, which allows for speedy data transfers up to 5 Gbps. On top of that, with up to 256GB of storage capacity, you'll have more than enough space to take what you need with you.

## Stores Data, Not Germs

---

Safety and hygiene are a top priority for the Blaze B07. A laboratory-certified antibacterial coating protects the drive and – most importantly – its users from germs. This is especially useful when sharing the drive with friends or with coworkers in an office environment.

## Ready, Inside And Out

---

On the inside, the Blaze B07 is always ready with True Plug & Play technology, which eliminates the need for external power. On the outside, a detachable cap protects the USB connector when not in use.

## Always With You

---

As it's meant to be an everyday item, the built-in straphole is a practical design choice to clip the Blaze B07 on to your keychain or bag, so it's always with you on the move. As long as you don't misplace your keys or bag, losing your data will be a thing of the past.

## Back-Up For The Back-Up

---

To ensure the safety of your data, the Blaze B07 comes with extra security measures. A free download of the SP Widget software is available for efficient file management and AES 256-bit encryption, while the Recuva File Recovery software provides data recovery. It's also backed by a limited 5-year warranty for even greater peace of mind.

## Specifications

---



- Capacity
  - 16GB, 32GB, 64GB, 128GB, 256GB
- Dimensions
  - 54.6mm x 18.9mm x 10.4mm

- Weight
- 7.9g
- Material
- Plastic
- Color
- Black
- Interface
- Type-A USB 3.2 Gen 1 (USB 3.1, USB 3.0, USB 2.0 compatible)
- Supported OS
- Windows 10/8.1/8/7/XP, Mac OS 10.3.X and above, Linux 2.6.X and above
- Operating Temperature
- 0°C - 70°C
- Certification
- CE, FCC, BSMI, UKCA, KC
- Warranty
- 5 year limited warranty

## Features

---

- Type-A USB 3.2 Gen 1 interface allows for speedy data transfers up to 5 Gbps
- Instant storage expansion up to 256GB capacity
- Laboratory-certified anti-bacterial coating protects the drive and its users from germs
- True Plug & Play Technology eliminates the need for external power
- Detachable cap protects the USB connector when not in use
- Built-in strap hole design for easy attachment to keychains or bags
- Recuva File Recovery allows for recovery of erased files, such as digital photos, documents, songs, and videos
- Free SP Widget software available for download for backup & restore, AES 256-bit encryption, and cloud storage

## Blaze B07

**16GB, 32GB, 64GB, 128GB, 256GB**

---

16GB

SP016GBUF3B07V1K

32GB

SP032GBUF3B07V1K

64GB

SP064GBUF3B07V1K

128GB

SP128GBUF3B07V1K

256GB

SP256GBUF3B07V1K