



CR80

SILVA CR80 is a lightweight, versatile, all-round headlamp designed for all types of outdoor activities. It is equally convenient when camping as it is when mountain hiking, on fishing trips, or when kayaking or climbing. With SILVA Intelligent Light[®], you always have a wide beam pattern nearest your feet at the same time as you can see where you are going. The light's output is 80 Lumens.

CR80 is water resistant and designed for Nordic conditions with changing weather conditions. SILVA's large on/off button is easy to operate even when wearing gloves.

FEATURES

- SILVA Intelligent Light®
- Water resistant (IPX6)
- Wide anti-slip headband
- 3 light modes
- Powered by 3 x AAA batteries
- Burn time TBC
- Large on/off button

ADVANTAGES

- A light ahead of you and also flow of light at your feet
- Withstands rain, snow and mud
- Stays comfortably on your head
- Provides flexibility in any user situation
- The batteries are easy to change when they run out
- Very good battery life
- Shows if you need to change batteries

Can be operated with gloves

BENEFITS

- Better control and higher speed
- Can be used in tough conditions
- Better outdoor experience
- Adjust the light output according to the terrain, speed, weather etc.
- No need of electricity for charging
- Minimum risk to run out of battery
- No need to change batteries "just in case" – good for the environment
- Perfect for use also in cold weather

ONE MINUTE DEMO

- 1. Turn the headlamp on
- 2. Go through the different light modes
- Inform about SILVA Intelligent Light[®] and the smart light distribution it provides
- 4. Turn the headlamp off





	CR80
USER CATEGORIES	Military use, outdoor work
PRODUCT FEATURES	
Light modes Helmet attach Bike attach Other	Max, min, blink No No Water resistant
SPECIFICATIONS	
LED type Intelligent Light® Number of battery types Burn time (Max mode) Burn time (Min mode) Burn tim (Blink mode) Charging time Charging type Battery indication Light distance (Max) Lumen IP-class Durability/drop test Temperature operating range Storage temperature Material Dimensions (lamp unit) Weight Instruction manual languages	2 x high power LEDS Yes 3xAAA 30h 90h 100h Not applicable No 40m 80 IPX6 Whitstand 2M drop onto wooden floor -20°C - +60°C -20°C - +60°C PC/ABS 55x34x35mm 52g (without batteries) 86g (including batteries) GB, DE, F, ES, I, NL, POR, SE, FI, CN (mandarin), JP, RUS
INCLUDED ACCESSORIES	
	Batteries, Quick guide
OPTIONAL ACCESSORIES	
DEALER INFORMATION	
Art. No. Gross weight (g) Qty inner/master pack Weight inner/master pack Dimensions inner/master pack (cm) Pgk type Country of origin Warranty Tariff code EAN (barcode and number)	37561 128g 5/60/360 640g 32x63x25mm Box China 2 years 8513100000 7318860196713

