

# Fuses 6.3 x 32

## Fuses, Slow-blow, Glass



Excellent I<sup>2</sup>T characteristics

Welded element for enhanced vibration tolerance

Glass cartridge, nickel plated brass end caps

### SPECIFICATION:

Characteristic (time/current)

Slow-blow

Rated voltage

250 VAC

Construction form

Glass tube

Dimensions  $\phi \times L$

6.3 x 32 mm

### PRODUCT RANGE:

Art. Nr.	Rated current	Breaking capacity
RND 170-00118	0.5 A	35 A@ 250 VAC
RND 170-00121	0.63 A	35 A@ 250 VAC
RND 170-00124	0.75 A	35 A@ 250 VAC
RND 170-00126	0.8 A	35 A@ 250 VAC
RND 170-00104	1 A	35 A@ 250 VAC
RND 170-00105	1.25 A	100 A@ 250 VAC
RND 170-00106	1.5 A	100 A@ 250 VAC
RND 170-00107	1.6 A	100 A@ 250 VAC
RND 170-00112	2 A	100 A@ 250 VAC
RND 170-00113	2.5 A	100 A@ 250 VAC
RND 170-00114	3 A	100 A@ 250 VAC
RND 170-00115	3.15 A	100 A@ 250 VAC
RND 170-00116	4 A	200 A@ 250 VAC
RND 170-00117	5 A	200 A@ 250 VAC
RND 170-00119	6 A	200 A@ 250 VAC
RND 170-00120	6.3 A	200 A@ 250 VAC
RND 170-00122	7 A	200 A@ 250 VAC
RND 170-00123	7.5 A	200 A@ 250 VAC
RND 170-00125	8 A	200 A@ 250 VAC
RND 170-00108	10 A	200 A@ 250 VAC
RND 170-00109	12 A	200 A@ 250 VAC
RND 170-00110	12.5 A	200 A@ 250 VAC
RND 170-00111	15 A	200 A@ 250 VAC