



OTTERBOX STANDARD CABLE / USB-A to USB-C

DURABLE AND DEPENDABLE /

Waste no time and experience zero hassle keeping your devices charged with OtterBox Standard Cables. These cables are thoughtfully designed with industry-leading mobile expertise and proven quality that is durable and dependable. OtterBox Standard Cables are bend/flex-tested 3,000 times for dependable use and feature a flexible exterior cord coating for quality feel and finish. OtterBox Standard Cables are available in a variety of colors, cable lengths and connectors to satisfy every charging need. As the No. 1-most trusted brand*, OtterBox is leveraging 20+ years of industry-leading mobile expertise to master mobile power.

FEATURES /

- Durable, trusted and built to last
- Bend/flex-tested 3,000 times for dependable use
- Flexible exterior cord coating for quality feel and finish
- Designed to work flawlessly with your favorite OtterBox cases and accessories
- Limited lifetime warranty and no hassle customer service



*Additional colorways available for order. Contact your sales representative for timing and minimum order quantities.

TECH SPECS /

PRODUCT NAME	Standard Cable	DATA RATE	480 Mbps
CONNECTOR TYPE	USB-A to USB-C	COUNTRY OF ORIGIN	Vietnam
CABLE SPECIFICATION	USB 2.0	LANGUAGES	EN/FR/DE/ES/IT/PT/JA/KO/ZH/ZHT
CURRENT CAPACITY	3 AMPS	RETAIL CARTON DIMENSIONS	3.94-in x 3.94-in x 1.18-in 10.00-cm x 10.01-cm x 3.00-cm

SKU	LENGTH	WEIGHT	COLOR*	RETAIL UPC	MASTER CARTON QTY	MASTER CARTON DIMS	MASTER CARTON WEIGHT	RETAIL CARTON WEIGHT
78-52537	1M / 3.3FT	0.06-lb 26.50-g	BLACK	840104211854	80	17.32-in x 13.78-in x 9.45-in 44.00-cm x 35.00-cm x 24.00-cm	9.26-lb 4200.00-g	0.09-lb 42.00-g
78-52659	2M / 6.6FT	0.13-lb 58.50-g	BLACK	840104218273	80	17.32-in x 13.78-in x 9.45-in 44.00-cm x 35.00-cm x 24.00-cm	16.42-lb 7450.00-g	0.16-lb 74.50-g
78-52538	3M / 9.8FT	0.22-lb 102.00-g	BLACK	840104211861	40	17.32-in x 13.78-in x 5.12-in 44.00-cm x 35.00-cm x 13.00-cm	13.01-lb 5900.00-g	0.26-lb 118.00-g
78-52536	1M / 3.3FT	0.06-lb 26.50-g	CLOUD DREAM	840104211847	80	17.32-in x 13.78-in x 9.45-in 44.00-cm x 35.00-cm x 24.00-cm	9.26-lb 4200.00-g	0.09-lb 42.00-g
78-52660	2M / 6.6FT	0.13-lb 58.50-g	CLOUD DREAM	840104218280	80	17.32-in x 13.78-in x 9.45-in 44.00-cm x 35.00-cm x 24.00-cm	16.42-lb 7450.00-g	0.16-lb 74.50-g
78-52661	3M / 9.8FT	0.22-lb 102.00-g	CLOUD DREAM	840104218297	40	17.32-in x 13.78-in x 5.12-in 44.00-cm x 35.00-cm x 13.00-cm	13.01-lb 5900.00-g	0.26-lb 118.00-g
78-52662	1M / 3.3FT	0.06-lb 26.50-g	COBALT BLUE	840104218303	80	17.32-in x 13.78-in x 9.45-in 44.00-cm x 35.00-cm x 24.00-cm	9.26-lb 4200.00-g	0.09-lb 42.00-g
78-52663	1M / 3.3FT	0.06-lb 26.50-g	MAUVE ROSE	840104218310	80	17.32-in x 13.78-in x 9.45-in 44.00-cm x 35.00-cm x 24.00-cm	9.26-lb 4200.00-g	0.09-lb 42.00-g