



OTTERBOX STANDARD CABLE / Lightning to USB-A

DURABLE AND DEPENDABLE /

Waste no time and experience zero hassle keeping your devices charged with OtterBox Standard Cables. These cables are thoughtfully designed with industry-leading mobile expertise and proven quality that is durable and dependable. OtterBox Standard Cables are bend/flex-tested 3,000 times for dependable use and feature a flexible exterior cord coating for quality feel and finish. OtterBox Standard Cables are available in a variety of colors, cable lengths and connectors to satisfy every charging need. As the No. 1-most trusted brand*, OtterBox is leveraging 20+ years of industry-leading mobile expertise to master mobile power.

FEATURES /

- Durable, trusted and built to last
- Bend/flex-tested 3,000 times for dependable use
- Flexible exterior cord coating for quality feel and finish
- Designed to work flawlessly with your favorite OtterBox cases and accessories
- Limited lifetime warranty and no hassle customer service



*Additional colorways available for order. Contact your sales representative for timing and minimum order quantities.

TECH SPECS /

PRODUCT NAME	Standard Cable	DATA RATE	480 Mbps
CONNECTOR TYPE	Lightning to USB-A	COUNTRY OF ORIGIN	Vietnam
CABLE SPECIFICATION	MFi	LANGUAGES	EN/FR/DE/ES/IT/PT/JA/KO/ZH/ZHT
CURRENT CAPACITY	3 AMPS	RETAIL CARTON DIMENSIONS	3.94-in x 3.94-in x 1.18-in 10.00-cm x 10.00-cm x 3.00-cm

SKU	LENGTH	WEIGHT	COLOR*	RETAIL UPC	MASTER CARTON QTY	MASTER CARTON DIMS	MASTER CARTON WEIGHT	RETAIL CARTON WEIGHT
78-52526	1M / 3.3FT	0.06-lb 26.00-g	CLOUD DREAM	840104211748	80	17.32-in x 13.78-in x 9.45-in 44.00-cm x 35.00-cm x 24.00-cm	9.26-lb 4200.00-g	0.09-lb 42.00-g
78-52629	2M / 6.6FT	0.13-lb 58.00-g	CLOUD DREAM	840104218037	80	17.32-in x 13.78-in x 9.45-in 44.00-cm x 35.00-cm x 24.00-cm	16.42-lb 7450.00-g	0.16-lb 74.50-g
78-52525	1M / 3.3FT	0.06-lb 26.00-g	BLACK	840104211731	80	17.32-in x 13.78-in x 9.45-in 44.00-cm x 35.00-cm x 24.00-cm	9.26-lb 4200.00-g	0.09-lb 42.00-g
78-52630	2M / 6.6FT	0.13-lb 58.00-g	BLACK	840104218044	80	17.32-in x 13.78-in x 9.45-in 44.00-cm x 35.00-cm x 24.00-cm	16.42-lb 7450.00-g	0.16-lb 74.50-g
78-52638	1M / 3.3FT	0.06-lb 26.00-g	COBALT BLUE	840104218068	80	17.32-in x 13.78-in x 9.45-in 44.00-cm x 35.00-cm x 24.00-cm	9.26-lb 4200.00-g	0.09-lb 42.00-g
78-52639	1M / 3.3FT	0.06-lb 26.00-g	MAUVE ROSE	840104218075	80	17.32-in x 13.78-in x 9.45-in 44.00-cm x 35.00-cm x 24.00-cm	9.26-lb 4200.00-g	0.09-lb 42.00-g