

2-Post Server Rack with Casters - 42U

Product ID: 2POSTRACK42



Store your server, network and telecommunications equipment in this sturdy 42U rack. With a 2-post design, the rack saves floor space and its dual-post, open-depth design makes it broadly compatible with longer equipment.

The 2-post rack features four swiveling casters, so you can easily move it around in your server room, office or studio. It's easy to reposition or relocate the rack in order to connect your rack-mounted equipment to other devices throughout your workspace.

The durable dual-post server rack is made of heavy-gauge steel, instead of aluminum, to ensure a stable installation platform. The rack supports a static loading capacity of up to 600 lb. (272 kg), and it's compliant with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494), to provide a stable platform that eliminates the need for concrete mounting kits.

You can easily mount your ANSI/EIA RS-310-D compliant network equipment to the rack without using additional hardware. It features square mounting holes on the frame and a universal design that's compatible with most rack equipment.

The 2POSTRACK42 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Use in your server room or any location where telecommunication and networking equipment needs to be housed
- Create a portable video editing and production rack that you can move around your studio to interface with different equipment



Features

- Maximum portability with four swiveling casters for easy transportation
- Widely compatible with most rack-mountable equipment with square mounting holes and a 2-post open frame design
- Superior durability and stability with full-steel construction
- 42U of mounting space
- Mount standard networking equipment using standard cage nuts and screws
- Easy assembly at the point of installation for rapid deployment

Hardware		
	Warranty	2 Years
	Wallmountable	No
	Rack Type	2-Post
	Frame Type	Open Frame
	U Height	42U
	Special Features	Casters (Included)
		Easy Assembly
		U-Markings
	Mounting Rail Profile	C-Shape
	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
Performance		
	Weight Capacity (Stationary)	663.0 lb [300 kg]
Physical Characteristics		
	Color	Black
	Construction Material	Steel

Product



Measurements

Product Length 23.6 in [60 cm]

Product Width 23.5 in [59.7 cm]

Product Height 6.6 ft [2.0 m]

Weight of Product 52.1 lb [23.6 kg]

Product Height with

Casters

6.8 ft [2.1 m]

Packaging Information

Flat Pack (Assembly

Required)

Yes

Package Length 6.7 ft [2.1 m]

Package Width 8.5 in [21.7 cm]

Package Height 6.7 in [17.1 cm]

Shipping (Package)

Weight

66.2 lb [29.9 kg]

What's in the Box

Included in Package Bottom Supporting Beams

Vertical Rails

Horizontal Rails

Angle Support Beams

2" Heavy-Duty Casters

2" Heavy-Duty Locking Casters

M6 Screws

M6 Nuts

M6 Caster Screws

M6 Cage Nuts

M6 Rack Screws

Plastic Washers



	Hex	Key	4mm
--	-----	-----	-----

Quick Install Guide

*Product appearance and specifications are subject to change without notice.