

25U Open Frame Server Rack - 4 Post Adjustable Depth (23" to 41") Network Equipment Rack w/ Casters/ Levelers/ Cable Management (4POSTRACK25U)

**Product ID:** 4POSTRACK25U



The 4POSTRACK25U 25U Server Rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 25U rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40in) that make it easy to adapt the rack to fit your equipment.

This durable 4-post rack supports a static loading capacity of up to 1200lbs (544kg), and offers compliance with several industry rack standards (EIA/ECA-310, IEC 60297, DIN 41494) for a universal design that's compatible with most rack equipment.

For a complete server storage solution that saves you time and hassle, the rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securely fastening the rack to the floor if needed, providing you with additional stability to better suit your server environment.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Rack-mounting A/V equipment in a radio or television studio

## Features

- **The STARTECH.COM Advantage:** StarTech.com offers a 2-year warranty and free lifetime technical support on this 25U rack and has been the choice of IT professionals and businesses for over 30 years
- **Ultimate Versatility:** With an adjustable mounting depth of 23 to 41", this open frame server rack provides you with a customized data storage solution for your IT equipment
- **User Friendly:** This 25U rack offers easy-to-read markings for both rack units (U) and depth; it has a wide range of mounting depth adjustments that make it easy to adapt to fit your equipment
- **Built to Last:** This durable 4-post rack supports up to 1200 pounds (544 kilogram), has a total product height of 50.8 inch / 129 centimeter (with casters), 48 inch / 120 cm (without casters), and is EIA/ECA-310, IEC 60297, DIN 41494 compliant
- **Hassle-Free Set Up:** The server rack includes accessories such as casters, levelling feet and cable management hooks; the base is pre-drilled for securely fastening the rack to the floor if needed

---

### Hardware

Warranty	2 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Open Frame
U Height	25U
Special Features	Adjustable Mounting Rails
	Base Plate with Floor-Anchoring Holes
	Built-in Cable Management
	Casters (Included)
	Grounding Lug(s)
	Leveling Feet
	Easy Assembly
	U-Markings
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

**Performance**

Weight Capacity (Stationary)	1202.9 lb [544.3 kg]
------------------------------	----------------------

---

**Physical Characteristics**

Color	Black
Construction Material	Steel

---

**Product Measurements**

Product Length	3.4 ft [1.0 m]
Product Width	23.8 in [60.4 cm]
Product Height	4.0 ft [1.2 m]
Weight of Product	72.9 lb [33.0 kg]
Maximum Mounting Depth	3.3 ft [1.0 m]
Minimum Mounting Depth	22.0 in [56 cm]
Product Height with Casters	4.2 ft [1.3 m]

---

**Packaging Information**

Flat Pack (Assembly Required)	Yes
Package Length	5.0 ft [1.5 m]
Package Width	6.3 in [16.0 cm]
Package Height	7.9 in [20.0 cm]
Shipping (Package) Weight	77.4 lb [35.0 kg]

---

**What's in the Box**

Included in Package	Left Vertical Rail
	Right Vertical Rail
	Base Bracket



Corner Section

Center Section

Top Bracket

M8 Bolt

M8 Washer

M8 (13mm) Wrench

M6 (10mm) Wrench

Phillips Screwdriver

M6 Cage Nut

PVC Cup Washer

M6 Phillips Head Screw

Cable Management Hook

Hook Mounting Screw

Casters

Leveling Feet

M6 Screw

M6 Flat Washer

M6 Flange Nut

Grounding Wires

---

***\*Product appearance and specifications are subject to change without notice.***

