

Desk Mount Dual Monitor Arm - Desk Clamp / Grommet VESA Monitor Mount for up to 32 inch Displays - Ergonomic Articulating Monitor Arm - Height Adjustable/Tilt/Swivel/Rotating

Product ID: ARMDUAL2



Work in comfort while saving space. This highly functional desk mount dual monitor arm brings you a cost-effective and versatile solution to an ergonomic workspace. Enjoy a wide range of motion with the double-jointed crossbar design plus tilt, swivel, rotation and height adjustment.

The multi monitor mount gives you the flexibility to set-up your desktop your way. Each of the articulating arms extends a full 15.7" (39.9 cm) to adjust to your needs.

The flexible double joints on the arms give you numerous options to position your monitors. You can place your monitors to face you, or even turn your monitors right around, 180-degrees, to share your screen with others. If you choose, you can also tighten the joints, making your setup as stationary as you like.

The cross-bar design provides a clean and simple look, while keeping monitors aligned. Use the micro-adjustment knob to align your monitors perfectly.

Made of steel, the rugged two display arm securely supports two VESA mount (75x75, 100x100) monitors up to 32", with a weight capacity of 17.6 lb. (8 kg) per monitor.

The double monitor arm lets you smoothly and effortlessly adjust the position of your screens for optimum viewing. Tilt your monitors +45/-45 degrees. Swivel +90/-90 degrees to the left or right. Rotate your monitors to portrait or landscape position with the 360-degree rotary VESA plate.

Adjust your monitors to the desired height. The dual screen mount is height adjustable along the 17.4" (44.3 cm) pole.

The multiple monitor mount is easy to install, using the C-clamp to attach the mount to the edge of your desk, table, or counter or mounting it through a grommet hole. The detachable VESA plate makes it easy to attach or remove your monitor. The built-in cable management keeps your cables neatly tucked away.

ARMDUAL2 is backed by a StarTech.com 5-year warranty and free, lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Mount two displays to your desk, table or counter using the desk clamp or grommet hole mount
- Create a dual-monitor set-up for shared office workstations, or for industrial and warehouse environments
- Rotate displays to portrait orientation for web design and coding

Features

- **32 INCH LARGE MONITOR SUPPORT:** VESA 75x75mm / 100x100mm compatible multi monitor mount supports 2 large monitors up to 32" (17.6 lb / 8 kg) per arm w/ horizontal articulation & basic height adjustment
- **WIDE RANGE OF MOTION:** Double monitor mount increases ergonomic comfort and productivity with +45/-45 tilt, +90/-90 swivel, 360 rotating display, and adjustable height along the 15.7" (39.8 cm) pole
- **ADJUSTABLE SET UP:** Use the desk-clamp (C-clamp) or grommet to easily mount and tighten by hand. Adjust the height and angle quickly with the included tools attached to the cable management clips
- **EASY DISPLAY ROTATION:** This desk mount dual monitor arm has articulating arms that support toolless monitor rotation from landscape to portrait positioning for viewing longer pages without scrolling
- **SMALL FOOTPRINT:** Space-saving design enhances the work area and built-in adjustable cable management clips along the arms and center pole keep cables organized for a presentable workspace

Hardware

Warranty	5 Years
Wallmountable	No
# of Displays Supported	2
Articulating	Yes
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.46 in. (10 - 88 mm) Grommet Clamp: Table Thickness 0.39 - 2.95 in. (10 - 75 mm) Grommet Mount Hole Size: 0.39 - 2.95 in. (10 - 75 mm)

Performance

Weight Capacity (Per Display)	17.7 lb [8 kg]
Maximum Display Size	32in
Height Adjustment	Yes
Maximum Arm Span	15.7 in [39.9 cm]
Display Tilt	+ 45 / - 45
Display Swivel	+90 / - 90
Swivel / Pivot	+/- 90 around the support post +/- 180 at the shoulder +/- 90 at the elbow
Display Rotation	360

Physical Characteristics

Color	Black
Construction Material	Steel
Product Length	19.7 in [50.0 cm]
Product Width	38.0 in [96.5 cm]
Product Height	21.6 in [54.8 cm]
Weight of Product	9.4 lb [4.2 kg]

Packaging Information

Package Length	17.7 in [45.0 cm]
Package Width	9.8 in [25.0 cm]
Package Height	5.3 in [13.5 cm]
Shipping (Package) Weight	9.4 lb [4.2 kg]

What's in the Box

Included in Package	VESA Mounts
---------------------	-------------



Swivel Arm Assembly
Desk Clamp Assembly
Pole
Pole Cap
Cable Management Clips
Grommet Base Plate
Micro Adjustment Knobs
Micro Adjustment Knob Screws
Rubber Pads
Pole Assembly Screws
Grommet Plate
3mm Hex Key
4mm Hex Key
6mm Hex Key
M4 x 12 mm Screws
M4 x 16 mm Screws
M5 x 12 mm Screws
M5 x 16 mm Screws
Washers
Spacers
Swivel Arm Cable Clips
User Manual

****Product appearance and specifications are subject to change without notice.***

