

Desk Mount Monitor Arm - Heavy Duty Ergonomic VESA Monitor Arm - Single 9kg Display - Full Motion, Height Adjustable, Articulating - Aluminum - C-Clamp/Grommet - Silver

**Product ID:** ARMPIVOTHD



Free up space while creating a more comfortable and productive work environment. This desk-mount monitor arm makes it easy to mount your VESA mount (75x75, 100x100) display above your desk or table and adjust the height with one touch for ideal viewing. Its sleek silver finish enhances the aesthetics of your workspace.

This heavy-duty aluminum monitor arm helps you save space, by securely mounting a computer monitor from 13" to 34" in size and up to 19.9 lb. (9 kg) in weight. It's ideal for many different office applications, such as healthcare or financial settings, shared workspaces, or when you wish to show your display to clients or colleagues.

The single monitor arm provides one-touch height adjustment, with a gas-spring cylinder that makes it easy to raise or lower your display. Adjust the tension according to the weight of your monitor, so you can re-position the monitor height effortlessly. The monitor mount provides 13.1" (335 mm) of height adjustment.

The full-motion articulating arm makes it easy to find the right viewing angle. Swivel your monitor 180 degrees to share your display. The articulating arm also supports 180-degree rotation, for landscape or portrait orientation. For comfortable viewing, tilt your screen +90 to -90 degrees.

Made of aluminum, the single monitor mount requires minimal assembly and is easy to install with the desk clamp or grommet mount. A detachable VESA mount panel makes it simple to attach or remove your monitor. Built-in cable management helps keep your cables organized.

The ARMPIVOTHD is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Use in workstations with multiple users

- Add comfort to office environments or your home office
- Rotate your display from landscape to portrait position for web design or coding

## Features

- **LARGE MONITOR MOUNT:** VESA 75x75mm/100x100mm compatible heavy-duty monitor arm for a single large 32" (16:9) or 43" (32:9/ultrawide) display up to 19.9lb/9kg; Full motion articulation & silver finish
- **WIDE RANGE OF MOTION:** Articulating ergonomic monitor arm increases comfort & productivity w/ +/-90 tilt, +/-90 swivel, 90 rotating screen (landscape/portrait), & 360 rotating computer monitor arm
- **ONE-TOUCH ADJUSTMENT:** Max height of 19.9" from the desk, the spring-assisted LCD monitor arm offers toolless height adjustable range of 13.2" and can extend outwards up to 23.8" away from base
- **EASY INSTALLATION:** C-clamp or grommet mount by hand to a desk (10 mm to 80 mm); detachable VESA plate w/ quick release clip makes mounting displays easy; tools incl. to adjust articulation tension
- **SMALL FOOTPRINT:** Aluminum desk mount monitor arm w/ space-saving design enhances the work area & cable management channels keep cables organized & hold incl. tool for articulation tension adjustment

---

## Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
Articulating	Yes
# of Displays Supported	1
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.39 - 3.34 in. (10 - 85 mm) Grommet Clamp: Table Thickness 0.39 - 3.14 in. (10 - 80 mm) Grommet Mount Hole Size: 0.41 - 1.96 in. (10.5 - 50 mm)

---

## Performance

Weight Capacity (Per Display)	19.9 lb [9 kg]
Minimum Display Size	13"

Maximum Display Size	34"
Fits Curved Display	Yes
Fits UltraWide Displays	Yes
Minimum Height	6.7 in [17 cm]
Maximum Height	19.9 in [50.5 cm]
Maximum Arm Extension	23.8 in [60.5 cm]
Display Tilt	+90 / - 90
Swivel / Pivot	180
Display Rotation	180

---

#### Special Notes / Requirements

Note	This mount supports monitors up to 34", including flat screen, curved and ultrawide displays, with a max weight of 19.9 lb. (9 kg). If you choose to use an ultrawide display in portrait position, the mount supports ultrawide displays with a max width of 35" (88.9 cm).
------	--

---

#### Physical Characteristics

Color	Silver
Material	Aluminum
Product Length	3.8 in [96.0 mm]
Product Width	11.2 in [28.4 cm]
Product Height	20.8 in [52.9 cm]
Weight of Product	6.8 lb [3.1 kg]

---

#### Packaging Information

Package Length	19.5 in [49.5 cm]
Package Width	12.6 in [32.0 cm]
Package Height	4.4 in [11.3 cm]
Shipping (Package)	9.9 lb [4.5 kg]



Weight

---

**What's in the Box**

Included in Package	spring arm
	VESA monitor mount
	grommet base plate
	grommet plate
	L bracket
	desk clamp
	clamp screws
	grommet knob
	rubber pads
	hex key holder
	4 mm hex key
	5 mm hex key
	6 mm hex key
	M4x12 mm thumbscrews
	M5x12 mm screws
	grommet screw
	washers
	spacers
	instruction manual

---

***\*Product appearance and specifications are subject to change without notice.***

