

HDMI or DVI to DisplayPort Active Converter

Product ID: HDMI2DP



The HDMI2DP DVI or HDMI to DisplayPort Converter converts an HDMI, DVI or Mini DVI input signal into a DisplayPort (or Mini DisplayPort) output, eliminating the cost of upgrading your source device hardware or purchasing a new display.

With support for full HD resolutions up to 1920x1200, the HDMI2DP converter is the perfect solution for connecting devices that have an HDMI, DVI single-link or mini DVI output, such as video cards (desktop or laptop), video game consoles or home theater receivers, to your DisplayPort-capable display.

To connect a DVI video source to this adapter, a DVI to HDMI adapter is required. The following StarTech.com adapters are compatible with this adapter:

3 ft HDMI to DVI-D Cable (HDDVIMM3)

6 ft HDMI to DVI-D Cable (HDMIDVIMM6)

8in HDMI to DVI-D Video Cable Adapter (HDDVIMF8IN)

HDMI to DVI-D Video Cable Adapter - M/F (HDMIDVIMF)

Mini DVI to HDMI Video Adapter for Macbooks and iMacs (MDVIHDMIMF)

The HDMI2DP is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays

- Keep your existing DisplayPort monitor to be used with your HDMI or DVI device

Features

- Supports full HD resolutions up to 1920x1200
- Stores EDID information to ensure compatibility between source and display
- Supports HDMI uncompressed 2-channel audio such as LPCM
- Allows for conversion of DVI or mini-DVI sources with additional cables (not included)
- Compatible with HDMI, DVI and Mini DVI 1.0 Input
- Supports DisplayPort/Mini DisplayPort 1.1a output

Hardware

Warranty	2 Years
Active or Passive Adapter	Active
AV Input	HDMI
AV Output	DisplayPort
Audio	Yes

Performance

Maximum Digital Resolutions	1920x1200 (50/60Hz)
Audio Specifications	5.1 Surround Sound

Connector(s)

Connector A	HDMI (19 pin)
Connector B	DisplayPort (20 pin)

Indicators

LED Indicators	Red Power LED
----------------	---------------

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC



Input Current	0.5A
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	5

Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	5% to 90% RH (no condensation)

Physical Characteristics

Color	Black
Material	Steel
Product Length	3.2 in [82 mm]
Product Width	1.7 in [43 mm]
Product Height	0.9 in [23 mm]
Weight of Product	3.8 oz [109 g]

Packaging Information

Package Length	6.1 in [15.6 cm]
Package Width	8.9 in [22.7 cm]
Package Height	2.1 in [54 mm]
Shipping (Package) Weight	13.8 oz [392 g]

What's in the Box

Included in Package	HDMI to DisplayPort converter
	Universal power adapter: comes ready for NA/EU/UK only when



you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand

Instruction Manual

****Product appearance and specifications are subject to change without notice.***

