

1 m (3 ft.) USB Multi Charging Cable - USB to Micro-USB or USB-C or Lightning for iPhone / iPad / iPod / Android - Apple MFi Certified - 3 in 1 USB Charger - Braided

**Product ID:** LTCUB1MGR



This USB multi-charging cable a single-cable solution that makes it easy to charge and sync your Apple Lightning or Android devices.

Keep this USB to Micro-USB, USB-C or Lightning cable on hand for all your charging needs, instead of carrying multiple cables. The 3-in-1 cable makes it easy for you to switch between different device models and platforms. Note that it will only connect to one device at a time.

Charge your devices from a USB wall charger, car charger, or power bank. The longer cable offers a greater range, so you can access your device conveniently even while it's connected to a charger.

With a braided nylon jacket, this durable charging cable doesn't kink or tangle as easily as non-braided cables do. It's an excellent replacement for any of your charging cables.

To charge or sync a USB-C or Lightning mobile device, simply attach the corresponding connector to the Micro-USB connector and plug into your device. To charge or sync a Micro-USB device, plug just the middle connector of the cable into your mobile device.

The cable will only charge or sync one device at a time.

LTCUB1MGR is Apple MFi certified and backed by StarTech.com 2-year warranty to ensure dependable performance.

## Certifications, Reports and Compatibility

## Applications

- Charge and sync your Apple Lightning, USB-C or Micro-USB mobile digital devices

## Features

- Carry a single cable for all your charging needs using this 3-in-1 charging cable
- Avoid kinks and tangles with the cable's nylon-braided jacket
- Charge or sync one Micro-USB, USB-C or Lightning device at a time
- Charge/Sync a USB-C or Lightning device -- attach the corresponding connector to the Micro-USB connector and plug into your device
- Charge a Micro-USB device -- simply plug the middle connector into your device

---

### Hardware

|                       |                                |
|-----------------------|--------------------------------|
| Warranty              | 2 Years                        |
| Connector Plating     | Nickel                         |
| Cable Jacket Material | Braided                        |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

---

### Performance

|               |                      |
|---------------|----------------------|
| Type and Rate | USB 2.0 - 480 Mbit/s |
|---------------|----------------------|

---

### Connector(s)

|             |                                       |
|-------------|---------------------------------------|
| Connector A | USB Type-A (4 pin) USB 2.0            |
| Connector B | Apple Lightning Connector (8-pin)     |
|             | USB Type-C (24-pin) USB 2.0 (480Mbps) |
|             | USB Micro-B (5 pin)                   |

---

### Physical Characteristics

|                 |                    |
|-----------------|--------------------|
| Color           | Silver             |
| Connector Style | Straight           |
| Wire Gauge      | 22/28 AWG          |
| Cable Length    | 39.4 in [100 cm]   |
| Product Length  | 39.4 in [100.0 cm] |

|                   |                  |
|-------------------|------------------|
| Product Width     | 0.6 in [15.0 mm] |
| Product Height    | 0.3 in [7.0 mm]  |
| Weight of Product | 1.3 oz [38.0 g]  |

---

#### Packaging Information

|                           |                  |
|---------------------------|------------------|
| Package Length            | 7.8 in [19.8 cm] |
| Package Width             | 5.9 in [15.0 cm] |
| Package Height            | 0.8 in [20.0 mm] |
| Shipping (Package) Weight | 3.0 oz [85.0 g]  |

---

#### What's in the Box

|                     |                                              |
|---------------------|----------------------------------------------|
| Included in Package | Lightning or USB-C or Micro-B to USB-A Cable |
|---------------------|----------------------------------------------|

---

***\*Product appearance and specifications are subject to change without notice.***

