

15U 19" Wall Mount Network Rack - Adjustable Depth 12-20" 2 Post Open Frame Server Room Rack for AV/Data/ IT Communication/Computer Equipment/Switch w/Cage Nuts & Screws

Product ID: RK15WALLOA



This open frame wallmount server rack provides 15U of storage, helping you to save space and stay organized. The equipment rack features an adjustable depth and can hold a total of up to 198 lb (90 kg).

The open frame rack adjusts from 12 to 20 inches (30.4 to 50.8 cm) to accommodate larger data, network, and telecommunication devices. The above-average depth also gives you the option to mount shelves and other accessories.

When space is limited you can wall-mount the open-frame rack in a server room, office, or above a doorway, to expand your workspace and ensure your equipment is easy to access.

The rack's open frame design promotes passive cooling; ensures easy access to your rack-mounted equipment and makes it simple to configure mounted devices, which saves you time.

With an adjustable depth as low as 12 inches (30.4 cm), this network rack is perfect for smaller spaces. It's easy to assemble and features wall-mounting holes that are spaced 12 and 16 in. apart, making it suitable for mounting on almost any wall, based on North American wall-frame stud-spacing standards.

Certifications, Reports and Compatibility

Applications

- Small office spaces
- When floor space is limited

Features

- **DURABLE & ADJUSTABLE:** This adjustable 15U 19" open frame wall mount network rack is EIA/ECA-310 compatible w/ 12-20" mounting depth supports most network switches like Cisco 2960
- **HEAVY DUTY:** This heavy duty 2 post open frame rack supports unobstructed airflow and is easy to install w/ a durable design made from SPCC cold-rolled steel with support for up to 200lbs of equipment
- **CERTIFIED PACKAGING:** The rack ships flat packed with ISTA-6 certified packaging to ensure complete and undamaged delivery and also features comprehensive assembly instructions
- **ACCESSORIES INCLUDED:** The wall mount server room/ computer/communication/AV/IT equipment rack includes a complete set of screws & cage nuts to securely mount all of your equipment in the rack
- **STARTECH.COM ADVANTAGE:** IT professionals choice for over 30 years; this 2-post adjustable wallmount rack is backed for 5 years by StarTech.com, including free 24/5 North America based multi-lingual tech support

Hardware

Warranty	5 Years
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	15U
Special Features	Adjustable Mounting Rails Easy Assembly U-Markings Wall-Mountable
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E
General Specifications	Internal Depth Range: 30 cm to 50.3 cm (11.8 inches to 19.8 inches)

Performance

Weight Capacity	198.9 lb [90 kg]
-----------------	------------------

Physical Characteristics



Color Black

Construction Material Steel

Product Measurements

Product Length 20.1 in [51.0 cm]

Product Width 19.8 in [50.4 cm]

Product Height 30.4 in [77.3 cm]

Weight of Product 33.5 lb [15.2 kg]

Maximum Mounting Depth 19.9 in [50.6 cm]

Packaging Information

Flat Pack (Assembly Required) Yes

Package Length 31.5 in [80.0 cm]

Package Width 20.9 in [53.0 cm]

Package Height 5.1 in [13.0 cm]

Shipping (Package) Weight 39.3 lb [17.8 kg]

What's in the Box

Included in Package

- Vertical Rails
- Front Horizontal Brackets
- Rear Horizontal Brackets
- M6 Cage Nuts
- M6 Screws
- Plastic Washers
- Assembly Screws
- Flat Washers
- Bolts
- User Manual

****Product appearance and specifications are subject to change without notice.***

