

4U 19" Desktop Open Frame Rack - 2 Post Free-Standing Network Rack Switch Depth for Patch Panel/Data/AV/IT/Communication/Studio/Computer Equipment 66lb Capacity w/Cage Nuts/Screws

## Product ID: RK4OD



This open frame desktop rack provides 4U of storage space for mounting smaller A/V and IT equipment.

With this 2 post data rack, you can mount equipment at a fraction of the cost of conventional racks. The floor standing rack is engineered to meet EIA-310 rack-mount standards and is constructed of solid steel, ensuring a sturdy and safe mounting solution for your mission-critical equipment.

The 4u desktop rack features an open frame, free standing design that saves space with a small footprint. It gives you the ability to place rack-mount equipment on any surface in your office, such as your desk. This makes it easy to access your equipment on a frequent basis.

The free standing network rack is easy to assemble and includes a pack of 16 M5 screws and cage nuts. If you're looking for a desktop mounting solution with more rack units, StarTech.com also offers 8U and 12U 2-post desktop computer racks.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

The RK4OD is backed by a StarTech.com lifetime warranty and free technical support.

## **Certifications, Reports and Compatibility**

## Applications

• Save space in your SoHo (small office, home office) or server room, by placing equipment on desks or other surfaces, instead of taking up floor space



• Place patch panels and other compact rack equipment neatly on or beside your desk

## Features

• 2-POST 4U DESKTOP OPEN FRAME RACK: Ideal for use on a workbench or in the back room of small office spaces without dedicated wiring closets; offers easy access to IT equipment like switches or routers

• DESIGNED FOR EASY ACCESS: Small size & 4U height of the free standing network rack is ideal for testing environments where easy front & rear access to equipment & frequent device changes are required

• TECH SPECS: 4U Open Frame Rack 19" Wide 2 Post EIA/ECA-310-E Compliant U Heights Marked 66.3lb (30 kg) Capacity M5 Cage nuts & screws incl. TAA Compliant

• EASY TO SHIP & SET UP: Quick and easy assembly combined w/5.4lb (2.5 kg) shipping weight makes the AV/studio switch depth rack ideal for remote sites; ships w/cage nuts & screws for mounting equipment

• LIFETIME WARRANTY: StarTech.com offers 24 hour technical support and has been the choice of IT professionals for 30 years, conducting thorough compatibility and performance testing on all our products

Hardware		
	Warranty	Lifetime
	Wallmountable	No
	Rack Type	2-Post
	Frame Type	Open Frame
	U Height	4U
	Special Features	Easy Assembly
		U-Markings
	Mounting Rail Profile	G-Shape
	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
Performance	Weight Capacity	66.3 lb [30 kg]
Physical Characteristics		
	Color	Black



	Construction Material	Steel
Product Measurements		
	Product Length	11.5 in [29.3 cm]
	Product Width	19.7 in [50.0 cm]
	Product Height	9.3 in [23.5 cm]
	Weight of Product	3.8 lb [1.7 kg]
	Maximum Mounting Depth	13.5 in [34.3 cm]
Packaging Information		
	Package Length	6.3 in [16.0 cm]
	Package Width	21.6 in [54.9 cm]
	Package Height	4.9 in [12.5 cm]
	Shipping (Package) Weight	5.4 lb [2.4 kg]
What's in the Box	Included in Package	Left Base Bracket
		Right Base Bracket
		Left Vertical Rail
		Right Vertical Rail
		Front Base Bracket
		Rubber Feet
		M5x12 Assembly Screws
		M5x16 Screws
		M5 Cage Nuts
		Instruction Manual

\*Product appearance and specifications are subject to change without notice.