

Vertical Wall-Mount Server Rack - Solid Steel - 6U

Product ID: RK619WALLV



StarTech.com

This wall-mount bracket provides 6U of storage space to vertically mount your equipment on the wall. The 6U wall-mount rack is EIA-310-D compliant to ensure compatibility with any 19" rack-mount equipment, such as your power strips, telecommunication, network and A/V devices.

The 6U rack optimizes your working space by mounting equipment to your wall instead of taking up desk space or other surface area. It's perfect for your SoHo (small office, home office) environment, server room or any other location where available space is limited.

The wall rack is constructed of solid steel to ensure a sturdy and safe mounting solution for your expensive, mission-critical equipment. Also, because the wall mounting holes are positioned 16" apart, it exactly matches standard drywall construction framework to ensure simple and secure wall-stud anchoring. Cage nuts and screws are also included with the wall-mount bracket, to save you the hassle of sourcing separate mounting hardware.

To provide a suitable mounting solution for virtually any surface such as your wall, ceiling or desk, the 6U bracket features separate mounting patterns for both ceilings and walls. This means that you can mount the bracket vertically to your wall or horizontally to your ceiling or under your desk.

If you're looking for a mountable storage solution with fewer rack units, StarTech.com also offers a 1U wall-mount bracket, a 2U wall-mount bracket, a 3U wall-mount bracket and a 4U wall-mount bracket.

The RK619WALLV is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Install networking and telecommunication equipment flush against the wall

- Mount KVM switches or workstations under a desk or work bench to free up work space
- Use in your small office environment where you can't comfortably fit a full-sized rack

Features

- Save space in your office or server room by mounting IT or AV equipment vertically to a wall or horizontally under a desk or work bench
- Hassle-free setup with wall-mount installation holes spaced 16 in. apart, matching standard construction framework
- Easy equipment installation, with cage nuts and screws included
- 6U wall-mount design
- Constructed to meet the EIA-310 19" rack standards
- Made from solid steel for durability

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	6U
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	200.5 lb [90.7 kg]
-----------------	--------------------

Special Notes / Requirements

Note	Package includes 1" screws for mounting to wood surfaces, additional hardware will be required for other materials
------	--

Physical Characteristics

Color	Black
-------	-------



Construction Material Steel

Product Measurements

Product Length	6.0 in [15.2 cm]
Product Width	19.9 in [50.5 cm]
Product Height	11.1 in [28.2 cm]
Weight of Product	2.9 lb [1.3 kg]

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	20.9 in [53.1 cm]
Package Width	11.7 in [29.7 cm]
Package Height	6.5 in [16.4 cm]
Shipping (Package) Weight	4.8 lb [2.2 kg]

What's in the Box

Included in Package	Vertical Wallmount Bracket
	M5 Cage Nuts
	M5 Screws
	Wood Screws
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

