

## 6 Port USB 3.0 / USB 2.0 Combo Hub with 2A Charging Port – 2x USB 3.0 & 4x USB 2.0

**Product ID:** ST7320USBC



The ST7320USBC 6-Port USB 3.0/2.0 Combo Hub features a special high-output dedicated charging port which enables you to charge USB devices by providing up to 2A of power, or it can add 2x USB 3.0 and 4x USB 2.0 ports to a computer through a single USB 3.0 host connection.

The hub includes an external power adapter, which when connected enables charging some portable electronic devices (e.g. an iPhone or other Smartphone), even without a USB connection to a host computer.

Offering a unique design that features USB ports along 3 sides of the hub, as well as a combination of USB 2.0 and 3.0 ports, this versatile and flexible USB hub is ideal for both laptop and desktop computers.

The ST7320USBC USB 3.0/2.0 hub is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Add multiple USB 3.0 and USB 2.0 to a computer system to support more device connections
- Charge a Smartphone
- Charging high-powered portable devices (such as tablets) which require special high output USB ports for charging
- Make USB ports that are hard to access more accessible, by being positioning the hub in a convenient location (within cable reach)
- Extend the range of a USB device by having the hub act as a mid-point repeater

## Features

- 2x USB 3.0 and 4x USB 2.0 ports that can be all accessed simultaneously
- 2 Amp high output USB Dedicated Charging Port (DCP)
- Includes 20 watt power adapter and host USB 3.0 cable
- Universal, multi-platform compatible, with no additional drivers or software required
- SuperSpeed USB 3.0 compliant host interface, with support for up to 5 Gbps of data bandwidth

---

### Hardware

Warranty	2 Years
USB-C Device Port(s)	No
USB-C Host Connection	No
Fast-Charge Port(s)	Yes
Ports	7
Interface	USB 3.0
Bus Type	USB 3.0
	USB 3.0
Chipset ID	VIA/VLI - VL813

---

### Performance

Type and Rate	USB 3.0 - 4.8 Gbit/s
	USB 2.0 - 480 Mbit/s

---

### Connector(s)

External Ports	USB Type-A (9 pin) USB 3.0 (5 Gbps)
	USB Type-B (9 pin) USB 3.0
	USB Type-A (4 pin) USB 2.0

---

### Software

OS Compatibility	OS Independent
------------------	----------------

---

### Special Notes / Requirements



System and Cable Requirements Available USB 3.0 or 2.0 port

---

**Indicators**

LED Indicators Power

---

**Power**

Power Source AC Adapter Included

Input Voltage 100 - 240 AC

Input Current 1.5 A

Output Voltage 5 DC

Output Current 4 A

Plug Type H

Power Consumption (In Watts) 20

---

**Environmental**

Operating Temperature 0C to 85C (32F to 185F)

Storage Temperature -10C to 95C (14F to 203F)

Humidity 5~90% RH

---

**Physical Characteristics**

Color Black

Form Factor Desktop

Material Plastic

Product Length 3.9 in [99.0 mm]

Product Width 2.4 in [60.0 mm]

Product Height 0.8 in [20.0 mm]

Weight of Product 2.6 oz [74.0 g]

---

**Packaging Information**

Package Quantity 1



Package Length	5.5 in [14.0 cm]
Package Width	4.7 in [12.0 cm]
Package Height	3.2 in [82.0 mm]
Shipping (Package) Weight	14.5 oz [412.0 g]

---

**What's in the Box**

Included in Package	6 Port USB Hub
	USB 3.0 Cable
	Universal Power Adapter (NA/JP, EU, UK, ANZ)
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

