

#### 4 Port Black PS/2 KVM Switch Kit with Cables

#### Product ID: SV411K



The SV411K 4 Port Black PS/2 KVM Switch Kit with cables lets you control four computers using a single keyboard, mouse and VGA monitor and offers both hotkey and top panel push-button operation for simple switching between connected computers.

Designed to integrate seamlessly into any environment, the KVM switch offers a small footprint design (roughly the size of a deck of playing cards) and draws power from the connected computers, so it doesn't require an external power supply.

Delivering dependable and convenient control of multiple computers from a single peripheral station, the KVM switch supports video resolutions of up to 2048 x 1536 and includes 3-in-1 (PS/2 and Video) cables to provide a complete, out-of-the-box KVM solution.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support.

# Certifications, Reports and Compatibility

# **Applications**

- Control 4 USB-enabled computers using a single keyboard, mouse, and VGA monitor
- Ideal for call centers, help desks, education environments, video editing, and PC enthusiasts
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors, keyboards and mice
- Multiple system control for single user workstations, increasing user productivity in the office



### **Features**

- Unique 3-in-1 cables included prevent keyboard and mouse connectors from becoming loose
- Supports PS/2 keyboard and mouse emulation for error-free PC boot
- All cables are connected to the rear for a more secure and neat connection
- Keyboard and mouse allow for hot plugging without having to turn either the KVM or the PC off
- Supports M/S IntelliMouse(Pro), Explorer, Optical mice
- Auto Scan Interval: 3, 8, 15, 30 seconds

Hardware			
	Warranty	2 Years	
	Audio	No	
	KVM Ports	4	
	PC Interface	PS/2	
	PC Video Type	VGA	
	Number of Monitors Supported	1	
	Rack-Mountable	No	
	Cables Included	Yes	
	Daisy-Chain	No	
Performance			
	On-Screen Display	No	
	DVI Support	No	

IP Control No

Hot-Key Selection Yes

Maximum Cable Length 2 x 4ft(1.2m) and

2 x 6ft( 1.8m) included

Maximum Analog Resolutions

1920 x 1440



Maximum Number of

Users

Port Selection Support Push Button and Hotkeys

**MTBF** 144000 hours

Connector(s)

Console Interface(s) PS/2 (6 pin, Mini-DIN)

VGA (15 pin, High Density D-Sub)

**Host Connectors** VGA (15 pin, High Density D-Sub)

**Software** 

**OS** Compatibility OS independent; No software or drivers required

**Power** 

**Power Source** Not Included (not required for standard applications)

**Physical** Characteristics

> Color Black

Material **Plastic** 

Product Length 7.3 in [18.5 cm]

**Product Width** 3.4 in [86 mm]

**Product Height** 0.9 in [22 mm]

Weight of Product 11.6 oz [328 g]

**Packaging** Information

> Package Length 9.3 in [23.7 cm]

> Package Width 7.2 in [18.4 cm]

Package Height 3.7 in [94 mm]

Shipping (Package) Weight

2.8 lb [1.3 kg]

What's in the Box

Included in Package

4 Port Compact KVM switch



Set of rubber feet

Instruction Manual

\*Product appearance and specifications are subject to change without notice.