

6in Micro USB Cable - A to Micro B

Product ID: UUSBHAUB6IN



The UUSBHAUB6IN 6-inch USB A to Micro-B cable provides a high quality connection between Micro USB-equipped USB 2.0 mobile devices (such as BlackBerry or Android-based smart phones, digital cameras, PDAs, Tablet PC devices and GPS systems) and a USB-capable computer, for everyday tasks such as data synchronization and file transfers.

This high quality cable is backed by StarTech.com's Lifetime Warranty to ensure dependable, long-lasting connections between Micro USB and USB devices.

Certifications, Reports and Compatibility

Applications

- An ideal replacement cable for connecting mobile devices to a USB capable computer

Features

- 1x USB 'A' male connector
- 1x USB Micro 'B' male connector
- Offers 6" in cable length
- Aluminum-Mylar Foil with Braided Shielding
- Supports high-speed USB data transfer rates of up to 480 Mbps

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Type and Rate	USB 2.0 - 480 Mbit/s
---------------	----------------------

Connector(s)

Connector A	USB Type-A (4 pin) USB 2.0
Connector B	USB Micro-B (5 pin)

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-10C to 30C (14F to 86F)
Humidity	30%-75% RH

Physical Characteristics

Color	Black
Wire Gauge	24/30 AWG
Cable Length	6.0 in [15.2 cm]
Product Length	6.0 in [15.2 cm]
Product Width	0.6 in [15.4 mm]
Product Height	0.3 in [7.6 mm]
Weight of Product	0.4 oz [10.0 g]

Packaging Information

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.3 in [8.0 mm]
Shipping (Package) Weight	0.6 oz [16.0 g]



What's in the Box

Included in Package	6in Micro USB Cable - A to Micro B
---------------------	------------------------------------

****Product appearance and specifications are subject to change without notice.***

