

8U Wall Mount Network Rack- 14 Inch Deep(Low Profile)- 19" Patch Panel Bracket for Shallow Server and IT Equipment, Network Switches- 80lbs/36kg Weight Capacity, Black

Product ID: WALLMOUNT8



This wall-mount bracket provides 8U of space for mounting shallow rack-mount equipment that's 13.75 in. (34.93 cm) deep or less to the wall, such as patch panels or network switches.

The 8U rack optimizes your working space by efficiently mounting your shallow equipment on your wall instead of taking up desk space or other usable surface areas. It's the perfect solution for your space-limited SoHo (small office, home office) environment or server room because it doesn't take up any floor space.

The wall rack is constructed of solid steel to ensure a sturdy and safe mounting solution for your mission-critical equipment. Also, because the wall rack's mounting holes are positioned 16 in. apart, it exactly matches standard drywall construction framework to ensure simple and secure wall-stud anchoring.

The rack also features a rear access panel that can be used to easily run cabling into the rack.

Cage nuts and screws are included with the wall-mount bracket, to save you the hassle of sourcing separate mounting hardware.

If you're looking for a shallow mounting solution with fewer or more rack units, StarTech.com also offers a 6U wall-mount bracket, and a 12U wall-mount bracket.

The WALLMOUNT8 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Mount equipment that is up to 14 inches deep on your wall

- Organize cabling or equipment in your network closet, wiring closet, back office or IDF
- Save space in your SoHo (small office, home office) or server room, by mounting equipment to the wall instead of taking up floor space

Features

- **8U WALL MOUNT RACK:** This 19 inch wide low profile wall mounted rack has a maximum mounting depth of 14 in [35 cm], recommended for networking equipment up to 12in deep, leaving 2in for cable routing; maximum weight capacity of 80 lbs [36kg]
- **Sturdy installation of mission-critical equipment,** with a solid steel design
- **COLD-ROLLED STEEL CONSTRUCTION:** The wall mounting data rack features a solid steel design for ultimate durability and to ensure a safe and sturdy mounting solution & includes wall mounting hardware; Installs onto 16" studs with mounting holes
- **STARTECH.COM ADVANTAGE:** IT professionals choice for over 30 years; this 8U wallmount rack backed for life by StarTech.com, including free 24/5 North America based multi-lingual tech support
- **EASY TO INSTALL:** The 8U wall mounting patch panel bracket ships fully assembled and comes complete with M6 Screws and M6 Cage Nuts for easier equipment installation, to save you the hassle of sourcing separate mounting hardware
- **EASY CABLE MANAGEMENT:** Built with efficiency in mind, the small wall mount patch panel bracket has rear cable routing access for easy cable organization in your network closet, server room, wiring closet, classroom

Hardware

| | |
|---------------------|---|
| Warranty | Lifetime |
| Wallmountable | Yes |
| Rack Type | 2-Post |
| Frame Type | Open Frame |
| U Height | 8U |
| Special Features | Ships Fully Assembled Wall-Mountable |
| Mounting Hole Types | Square (For Cage Nut) |
| Industry Standards | EIA/ECA-310-E |

Performance

| | |
|-----------------|-------------------|
| Weight Capacity | 80.2 lb [36.3 kg] |
|-----------------|-------------------|

Physical Characteristics

| | |
|-----------------------|-------|
| Color | Black |
| Construction Material | Steel |

Product Measurements

| | |
|------------------------|-------------------|
| Product Length | 13.8 in [34.9 cm] |
| Product Width | 19.7 in [50.0 cm] |
| Product Height | 14.3 in [36.2 cm] |
| Weight of Product | 12.5 lb [5.7 kg] |
| Maximum Mounting Depth | 13.8 in [34.9 cm] |

Packaging Information

| | |
|-------------------------------|-------------------|
| Flat Pack (Assembly Required) | No |
| Package Length | 20.6 in [52.2 cm] |
| Package Width | 15.0 in [38.2 cm] |
| Package Height | 15.4 in [39.2 cm] |
| Shipping (Package) Weight | 16.7 lb [7.6 kg] |

What's in the Box

| | |
|---------------------|--------------------|
| Included in Package | Wall-Mount Bracket |
| | M5 Cage Nuts |
| | M5 Screws |
| | M6 K-Nut |
| | Wood Screws |
| | User Manual |

**Product appearance and specifications are subject to change without notice.*

