

4U 19in Hinged Wall Mounting Bracket for Patch Panels

Product ID: WALLMOUNTH4



The WALLMOUNTH4 4U 19in Hinged Wall Mounting Bracket for Patch Panels is 6in deep and sturdily designed to provide a dependable solution for mounting a patch panel, or other slim 19in networking equipment to a wall.

The patch panel wall mount features a hinged design for easy access to configuration buttons, ports and cables. The wall mounting holes are spaced 16 in. apart, making it suitable for mounting on almost any wall, based on common wall-frame stud spacing.

Backed by a StarTech.com 2-year warranty.

Certifications, Reports and Compatibility

Applications

• Wall mount patch panels and other slim 19" rackmount equipment

Features

- Sturdy cold rolled steel construction
- 4U rack height
- Hinged side panel for easy equipment access
- 15 kg (33 lbs) weight capacity
- Wall mounting holes are 16" center to center for greater stability, and mounting to standard wall studs



Hardware		
	Warranty	2 Years
	Wallmountable	Yes
	Rack Type	2-Post
	Frame Type	Open Frame
	U Height	4U
	Mounting Rail Profile	L-Shape
	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
Performance		
	Weight Capacity	33.2 lb [15 kg]
Physical Characteristics		
	Color	Black
	Construction Material	Steel
Product Measurements		
	Product Length	6.0 in [15.2 cm]
	Product Width	19.7 in [50.1 cm]
	Product Height	7.0 in [17.9 cm]
	Weight of Product	4.9 lb [2.2 kg]
	Maximum Mounting Depth	5.8 in [14.8 cm]
Packaging Information		
	Flat Pack (Assembly Required)	No
	Package Length	20.5 in [52.0 cm]
	Package Width	7.8 in [19.8 cm]
	Package Height	7.4 in [18.7 cm]



	Shipping (Package) Weight	5.9 lb [2.7 kg]
What's in the Box		
	Included in Package	Wall-Mount Rack
		M6 Screws
		M6 Cage Nuts
		Plastic Washers
		Wall Screws
		Plastic Anchors

*Product appearance and specifications are subject to change without notice.

