

Wall-Mount Server Rack with Built-in Shelf - Solid Steel - 4U

Product ID: WALLSHELF4U



This wall-mount rack provides 4U of space for mounting your servers or A/V equipment to a wall. The rack also has a built-in shelf to create a sturdy surface for storing equipment that is not rack-mountable.

The wall-mount bracket features an adjustable mounting depth of 12 inches to 18 inches as well as a dual-position 12 in. shelf that can be at either the top or the bottom depending on rack's positioning. These two features allow you to customize both depth and layout to best fit your equipment and cables, ensuring that the rack suits your space.

The 4U rack wall mounting feature allows you to free up desk or floor space -- perfect for your SoHo (small office, home office) environment, server room or any other location with limited space available.

The wall rack is constructed of solid steel to ensure a sturdy and safe mounting solution for your mission-critical equipment and with the wall mounting holes positioned 16" apart, it exactly matches standard drywall construction framework, to ensure simple and secure wall-stud anchoring.

For hassle-free equipment installation, the rack features 10-32 tapped rails, so you can mount your equipment directly to the rail and avoid the hassle of using cage nuts.

The wall-mount rack comes in a flat-packed box to reduce shipping volume, which significantly reduces your costs in shipping while also providing greater protection than offered by pre-assembled racks. Packaged efficiently, you can easily store and transport the rack for deployment at a later date or in a different location than where it's received.

The WALLSHELF4U is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Install networking and telecommunication equipment flush against the wall

- Use in your small office environment where you can't comfortably fit a full-sized rack
- Store frequently used tools on the built-in shelf
- Place equipment that's not rack-mountable on the built-in shelf

Features

- Customize your setup with a built-in shelf that can be positioned at either the top or the bottom of the rack
- Save space in your office or server room by mounting IT or AV equipment to the wall
- Hassle-free setup with 10-32 tapped rails, enabling you to mount your equipment directly to the rail without cage nuts
- Adjustable mounting depth, from 12 in. to 18 in.
- 4U wall-mount design
- Constructed to meet the EIA-310 19" rack standards
- Made from solid steel for durability
- Tie-off points for cable management
- Rear opening for cable access

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	4U
Special Features	Adjustable Mounting Rails
	Easy Assembly
	Wall-Mountable
Mounting Rail Profile	L-Shape
Mounting Hole Types	Threaded Hole
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	75.2 lb [34.0 kg]
-----------------	-------------------

Physical Characteristics

Color	Black
-------	-------

Construction Material	Steel
-----------------------	-------

Product Measurements

Product Length	12.0 in [30.5 cm]
----------------	-------------------

Product Width	19.0 in [48.3 cm]
---------------	-------------------

Product Height	10.6 in [26.8 cm]
----------------	-------------------

Weight of Product	15.6 lb [7.0 kg]
-------------------	------------------

Maximum Mounting Depth	17.8 in [45.1 cm]
------------------------	-------------------

Packaging Information

Flat Pack (Assembly Required)	Yes
-------------------------------	-----

Package Length	19.7 in [50.0 cm]
----------------	-------------------

Package Width	15.0 in [38.0 cm]
---------------	-------------------

Package Height	1.6 in [40.0 mm]
----------------	------------------

Shipping (Package) Weight	17.0 lb [7.7 kg]
---------------------------	------------------

What's in the Box

Included in Package	back plate
	right bracket
	left bracket
	shelf bracket
	adjustable rails
	10-32 x 3/8 screws



10-32 mounting screws

mounting template

wood screws

instruction manual

****Product appearance and specifications are subject to change without notice.***

