Data sheet



Hot-melt glue applicator

GluePRO 300

EAN 4007841035280



Functional description

These days, hot-melt glue applicators are indispensable in industry and the trades. Particularly when it comes to professional use, factors such as quality, reliability and ergonomics are the key criteria. It is in this respect that the GluePRO 300 sets standards. Its sturdy quality and design are made for effortless, fatigue-free work. The stroke adjustment function makes it possible to set the quantity of glue per stroke for any specific application. The nonslip grip handle provides additional safety while working. Heating element and electronic components are designed to withstand long periods of rugged use. The GluePRO 300. The new benchmark.

Technical specifications

Output, heat-up phase	300 W
Average power consumption	90 W
Temperature	190 – 190 °C
Melt temperature	190 – 190 °C
Temperature accuracy +/-	3 °C
Warm-up time	3
Delivery rate	20 gr/min
Max. stick diameter	11.7 mm
Function, hanger	Yes
Soft grip	Yes
Stroke adjustment	Yes
Idle mode	No
Nozzle can be changed	Yes
Mains power supply	220 – 230 V , 50 / 60 Hz
Model	Folding box
PU1, net weight	0,580 kg
Manufacturer's Warranty	1 year