

Steinel: HL 2020 E – The Professional Hot Air Tool for the Serious DIYer!!!

- 20% higher durability!
- Optimised protection for you; n optical indication will warn against the danger of burnings at the end outlet; as well after switching-off of power!
- The joystick creates a completely new and intuitive operation plus control!

Technical Data:-

Dimensions (LxBxH):	253 x 86,5 x 200 mm
Voltage:	230V Euro Plug
Output:	2200 W
Temperature:	80 - 630 °C, electronically adjusted in 10°C steps
Airflow	150 / 300 / 500 l/min
Stages:	3 (Airflow)
Specials:	Reduction nozzle 9mm included, plastic case, optical warning against burnings, new intuitive operation, power cord exchangeable, optimised centre of gravity, display, hanger, optional new accessory: HL Scan and fine dust partical filter
Length power cord:	2,20 m
Motor:	Brush Motor
Heating element:	Ceramic Heating Element
Steinel UK Code:	012007
Bar Code:	4007841352202



**Included in delivery:-
Plastic case
& 9mm Reduction nozzle*

