

## 40x40x10 mm

## 5.4 CFM





## Specifications


MAGLev by SUNON	Bearing	Rating Voltage	Power Current	Power Consumption	Speed	Air Flow	Static Pressure	Noise	Weight	Curve
	<ul> <li>VAPO</li> </ul>	(VDC)	(mA)	(WATTS)	(RPM)	(CFM)	(inch-H₂O)	(dB(A))	(g)	
HA40101V4-1000U-A99	٠	12	31	0.38	5000	5.4	0.09	15.7	15.4	1

## Air Flow-Static Pressure Characteristics


External dimensions(mm)











\*All model could be customized. Please contact with Sunon Sales.

\*Specifications are subject to change without notice. Please Visit SUNON website at www.sunon.com for update information.