

**TEMPO TA201610**



Sample photo

**Order symbol:** TA201610  
**Product nbr:** 5814001  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074060730  
**El. number:**  
 Finland: 3435684  
 Denmark: 8212035027  
 Sweden: 5814001  
 Norway:

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		201	163	98	Ingress Protection (EN 60529): IP 65
<b>inch:</b>		7.9	6.4	3.9	Impact Resistance (EN 62262): IK 07
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
<b>Base colour:</b>		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
<b>Cover colour:</b>		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 650
<b>Cover screws material:</b>		Polyamide			<b>Certificates:</b>
<b>Cover screws colour:</b>		Grey			Fimko
<b>Gasket material:</b>		PUR			Gost R
<b>Temperatures:</b>					
<b>Short term:</b>		-40 ... 80 °C			
<b>Continuous:</b>		-40 ... 60 °C			
<b>Short term:</b>		-40 ... 175 °F			
<b>Continuous:</b>		-40 ... 140 °F			
<b>Accessories:</b>					
MP 2016		Mounting plate			
DH-3		DIN-35 Mounting rail			
ARH 2320		DIN-35 Mounting rail			
FP 10674		Wall fastening lug (2 pcs) incl. screws			
DPS 14553		Grey sealing plug set			

