

P/N: TA70

Copyright

© 2015, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Document identity

Publ. No.: TA70 Release: Commit: 29570 Language: en-US Modified: 2015-10-13 Formatted: 2015-10-17

Website

http://www.flir.com

Customer support

http://support.flir.com

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.



Part number	TA70
Part description	CAT IV Insulated Alligator Probes
 Works with FLIR TA80 test probes. Complies with latest UL CAT IV/CAT III—1000 V. Slide-on connection with finger guards. 2 year warranty. 	
Specifications	
Maximum capacity	10 A
Operating temperature	–10 to 50°C (14 to 122°F)
Relative humidity	Maximum relative humidity 80% for temperature up to 31°C (88°F) decreasing linearly to 50% relative humidity at 50°C (122°F)
Storage temperature	–20 to 60° C (–4 to 140° F), <80% relative humidity
Altitude	Operating below 2000 m (6562')
Meter data	
Suitable main unit	FLIR TA80 test leads
Warranty	2 years



P/N: TA70

© 2015, FLIR Systems, Inc. #TA70; r. /29570; en-US

Certifications	
Certifications	IEC/EN 61010-031:2008 and UL 61010- 031:2010 to 600 V CAT IV and 1000 V CAT III
Meter physical data	
Weight	0.02 kg
Dimensions (H \times W \times L)	7.94 cm × 4.13 cm × 1.91 cm
Material	Nickel-plated steel, TPR and polypropylene
Color	Black and red
Shipping information	
Packaging type	Color box
Packaging contents	Manual, TA70 alligator clips
Packaging weight	0.05 kg
Packaging dimensions (H \times W \times L)	7 .62 cm \times 2.54 cm \times 16.83 cm
Carton weight	3.3 kg
Carton dimensions	14.5" × 13" × 8"
Carton quantity	48
EAN-13	0793950377703
UPC-12	793950377703
Country of origin	Taiwan
Tariff code	9030908822
Technical support	
Website	http://support.flir.com
E-mail	TMsupport@flir.com
Phone	855-499-3662
Repairs	repair@flir.com