


Specification sheet : SP-DSR-019

Firm Address Zip / City Customercode : Distrelec Group AG Grabenstrasse 6 8606 NÄNIKON · : 13800342 / DSR

TBS partnumber Date Your partnumber : SP-DSR-019 20-4-2017

Coiled cable dimensions



0,37 kg/pc Weight: ±

Cable specification

:

: -40 °C to +70 °C

Cable type Stranding Conductor insulation Conductor colours Overall sheath Colour Temperature range

: LiF11Y11Y 1x2,50 mm2 TB17 FLEX : 322x0,10 mm bare copper wires : PUR : transparent PUR : yellow/green



Photographs are for illustrative purposes only

Tolerances ± 10% (dimensions and quantities)

Attention: Coiled cables, power cords and (cable)assemblies are customized products, specifically manufactured and supplied upon order. Therefore these products cannot be returned or exchanged in any way. Offer is non-committal, fixed price for up to 6 weeks, subjected to prior sale, subjected to technical changes, especially changes in measurement and construction. All our offers, orders granted to us and (project) contracts/agreements with us are subjected to the METAALUNIE TERMS AND CONDITIONS only. These terms and conditions have been filed at the Registry of the Rotterdam District Court.

The Best Solution De Slof 2 5107 RJ Dongen The Netherlands V.A.T.-nr.: NL 815889215B01

HR Eindhoven nr.: Rabobank Tilburg nr.: IBAN code : BIC code :

18048791 0304.1314.07 NL39 RABO 0304 1314 07 RABONL2U

+31 (0) 162 523 436 Phone : sales@the-best-solution.com www.the-best-solution.com E-mail Internet :