

TY175-50X



CBL TIE 50LB 7IN UV BLACK NYL



General Information

Extended Product Type	TY175-50X
Product ID	7TAG054360R0178
EAN	5414363060956
Catalog Description	CBL TIE 50LB 7IN UV BLACK NYL
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 186.43mm (7.34 Inches), Width of 4.674mm (0.184 Inches), Thickness of 1.24mm (0.049 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds), Bulk Pack

Ordering

EAN	5414363060956
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.003 lb 1.361 g
--------------------	--------------------

Container Information

Package Level 1 Units	1000 piece
Package Level 2 Units	10000 piece
Package Level 2 Width	12.7 in 323 mm
Package Level 2 Height	13.2 in 335 mm
Package Level 2 Depth / Length	18.3 in 465 mm

Additional Information

Brand / Label	Ty-Fast
Bundle Diameter	0.06 to 1.73 in 1.6 to 44 mm
Color	Black
Lock Type	Plastic Pawl

Material	Nylon/Polyamide 6.6 Weather Resistant
Number of Batteries	0
Product Name	PLASTIC CABLE TIE
Product Type	Black Cable Tie
Special Functions	The integrally formed nylon pawl combines low insertion and high locking strength.
Standards	UL E49405
Tensile Strength	50 lb 220 N
Thickness	0.049 in 1.24 mm
UPC	786210898575

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY175-50X
Instructions and Manuals	TY175-50X

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

