

# TY26M



CABLE TIE 40LB 11IN NATURAL NYLON



## General Information

Extended Product Type	TY26M
Product ID	7TAG009120R0002
EAN	5414363062738
Catalog Description	CABLE TIE 40LB 11IN NATURAL NYLON
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 284.4mm (11.08 Inches), Width of 3.71mm (0.14 Inches), Thickness of 1.31mm (0.05 Inches), Tensile Strength Rating of 180 Newtons (40 pounds), Bulk Pack

## Ordering

EAN	5414363062738
Customs Tariff Number	3926909990

## Dimensions

Product Net Weight	.003 lb 1.361 g
--------------------	--------------------

## Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	12 in 305 mm
Package Level 1 Depth / Length	18 in 457 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	13.25 in 337 mm
Package Level 2 Height	9.75 in 248 mm
Package Level 2 Depth / Length	21 in 533 mm

## Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	0.08 to 3 2 to 76.2 mm

Color	Natural
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES
Product Type	Standard
Special Functions	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Standards	UL E49405
Tensile Strength	40 lb 180 N
Thickness	0.05 in 1.31 mm
UPC	786210824680

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY26M
Instructions and Manuals	TY26M

### Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

### Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

