


## **Common Mode Choke**

**TCK-051** 


Order Code	TCK-051
Inductance (each winding)	<b>145 μH ±35%</b> (at 100 kHz / 100 mV)
Impedance (DCR)	20 mOhm max.
Rated Current	5.2 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C



## Impedance Curve



## **Outline Dimensions**



Dimensions [mm]	
11.5 max.	
11.5 max.	
8.8 max.	
2.5 min.	
7.62 ±0.2	
7.62 ±0.2	
ø 0.6 ±0.1	

© Copyright 2019 Traco Electronic AG

Specifications can be changed without notice.