

# TCP 12

Product no.: T0051005399N



## Benefits

- › 30/40 W, 12/14 V
- › With adapter PT 7 (370 °C) and soldering tip LT M
- › 3 m cord with battery clamps e.g. for car battery
- › For PT Soldering tips



### Technical Data

Active Tip heating element technology	---
Power Response heating element technology	---
Silver Line heating element technology	on
Voltage	12 V
Power	35 W
Tip range	LT, PT
Supply unit	---
WX-compatible	---
Temperature range °C	5 = 260 °C / 6 = 310 °C / 7 = 370 °C / 8 = 425 °C / 9 = 480 °C
Temperature range °F	5 = 500 °F / 6 = 600 °F / 7 = 700 °F / 8 = 800 °F / 9 = 900 °F
Heating time	t.b.d.
Safety rest	T0051502099
Safety rest (optional)	---
Barrel	T0058720794
Integrated direct extraction	Attachment T0052512599