16-Port Rackmount KVM Switch

TK-1603R (Version v2.0R)

- Controls up to 16 computers or servers
- Console port supports both USB and PS/2 for keyboard and mouse interfaces
- USB only for PC side mouse and keyboard connections
- Supports Windows®, Linux®, Mac OS® and more
- Supports up to 2048 x 1536 VGA resolution
- Auto-scan for monitored PCs with adjustable scan interval from 10-99 seconds
- Keyboard status restored when switching between computers
- LEDs display for easy status monitoring
- Audio notification for port switching confirmation (enable/disable)
- Keyboard hot-key command or push button switching
- Plug & Play and Hot-Pluggable
- Required cabling sold separately (TK-CU06 / TK-CU10 / TK-CU15)
- Standard 19" (1U) rackmount design
- 2 year warranty

Console Port Connectors	 Keyboard: USB Type A, PS/2 Mouse: USB Type A, PS/2 Monitors: VGA
Computer Interface (up to 16)	 Keyboard/Mouse: USB Type A Monitors: VGA
Monitor Resolution	• 2048 x 1536
Switching Control	Front panel push buttonsKeyboard hot key commands
Operating Temperature	 0° − 40° C (32° − 104° F)
Operating Humidity	• Max. 80 % non-condensing
Power	 Input: 100 - 240V AC, 50/60Hz, 0.8A Output: 9V DC, 1A external power adapter Max. consumption: 0.7W
Dimensions	• 407 x 165 x 45mm (16 x 6.5 x 1.8 in.)
Weight	• 2kg (4.5 lbs.)
Certifications	• CE • FCC
Warranty	• 2 year

PACKAGE CONTENTS

- TK-1603R
- Quick Installation Guide
- Power adapter (9V DC, 1A)
- Rackmount kit