


2-Port Dual Monitor DisplayPort KVM Switch

TK-240DP (v1.0R)

- Dual Monitor DisplayPort™ 1.2 KVM
- · Designed for use with Dual DisplayPort systems
- · 3.5mm speaker and microphone connections
- Supports 4K UHD resolutions up to 3840 x 2160
- · 2-Port USB 2.0 hub for storage devices and printers
- · Required cabling (TK-CP06) sold separately
- · No CD installation required

TRENDnet's 2-Port Dual Monitor DisplayPort KVM Switch, model TK-240DP, allows you to control two computers with one set of console controls. Experience up to 4K UHD resolutions, no driver installation required. The TK-240DP is designed for dual monitor systems with USB mouse and keyboard connections, and features a two-port USB hub to share storage devices or printers between computers.

TRENDIET




DisplayPort Monitor

Designed to connect to two DisplayPort monitors



4K UHD Resolution

Supports resolutions up to 4K UHD (3840 x 2160)



USB 2.0 Hub

Two additional USB ports to connect storage devices and printers.

Networking Solution





Computers

Control up to 2 computers



USB Mouse & Keyboard

True Transparent USB (TTU) emulation technology supports most keyboard and mouse designs



USB 2.0 Hub

Two additional USB ports to connect storage devices and printers



4K UHD

Supports resolutions up to 4K UHD (3840 x 2160)



DisplayPort Monitor

Designed to connect to two DisplayPort monitors



Hot Keys

Hot Key command shortcuts



Audio Support

Full audio support maximizes work station productivity



Housing

Rugged metal enclosure



Specifications

•	
Console Port Connectors	 Keyboard: USB Type A Mouse: USB Type A Monitors: 2 x DisplayPort 1.2 2-port USB 2.0 Hub Speaker jack: 3.5 mm Microphone jack: 3.5 mm
KVM Port Interface (up to 2)	Keyboard/Mouse: USB Type B Monitors: 2 x DisplayPort 1.2 Speaker jack: 3.5 mm Microphone jack: 3.5 mm
Computer Interface (up to 2)	Keyboard/Mouse: USB Type A Monitors: 2 x DisplayPort 1.2 Speaker jack: 3.5mm Microphone jack: 3.5mm
Monitor Resolution	• Up to 3840 x 2160
Switching Control	Front panel push buttons Keyboard hot key commands
Operating Temperature	• 0° – 40° C (32° – 104° F)
Operating Humidity	Max. 90 % non-condensing

Power	 Input: 100 - 240V AC, 50/60Hz, 0.8A Output: 9V DC, 2A external power adapter Max. consumption: 0.7W
Dimensions	• 163 x 100 x 66 mm (6.4 x 3.9 x 2.6 in.)
Weight	• 750g (1.65 lbs.)
Certifications	• CE • FCC
Warranty	• 2 year

PACKAGE CONTENTS

- TK-240DP
- · Quick Installation Guide
- Power adapter (9V DC, 2A)

All references to speed are for comparison purposes only. Product specifications, size, and shape are subject to change without notice, and actual product appearance may differ from that depicted herein.